


PORTABLE T-CLAMP DIRECT HEAT

KF-CS Series

Lightweight - Wide Serrated Seal Line



- Easy to operate
- Lightweight
- Variable temperature control
- Suitable for thicker materials
- Seal width: 15mm (0.59")
- Seal length: 200mm (7.9") and 30mm (11.8")
- Seal style: serrated
- Voltage: 110V or 220V

More Details:

KF-200CS and KF-300CS are portable direct heat sealers that are lightweight and easy to use anywhere. Our portable KF-sealers are ideal for sealing small, irregular, or extra long packages. We recommend using this sealer if you are sealing cellophane, coated aluminum foil, Kraft paper, and other thicker materials. Please note direct heat sealers cannot seal polyethylene material.

Equipped with an adjustable temperature controller, our KF-CS direct heat sealers allows the user to control the amount of heat needed for different material types. A 5-15 minute warm up time is required to achieve the correct temperature. The sealer is constructed of durable metal with insulated rubber hand grips. Also

included with each sealer is a stand for setting your sealer while not in use. Please DO NOT touch the jaws of the sealer until it has cooled down.

Depending on the material, allow 5-15 minutes of warm up time for the sealer to reach the desired temperature. Turn the temperature controller to the desired setting, the power and heat lamp will turn on. Just insert the material between the jaws and close the jaws for a few seconds. Release the jaw. Increase or decrease the timing until a satisfactory seal is obtained.

Specifications:

	KF-200CS	KF-300CS
Power Supply	110V / 220V	110V / 220V
Watts	120W	190W
Seal Width	15mm / 5/8"	15mm / 5/8"
Seal Length	200mm / 7.9"	300mm / 11.8"
Power Cord Length	8ft	8ft
Weight	4-lbs	4-lbs