

PORTABLE T-CLAMP IMPULSE

FKR-A SERIES SEALERS

Value Unit – Lightweight & Compact



- Available in 8", 12", 16" seal lengths
- Lightweight & easy to operate
- Impulse heat w/ timer
- Double impulse – two heating elements
- Recommended for poly materials such as polyethylene, polypropylene, PVC, PE laminated paper, and aluminum foil

FKR-A-Series Portable T-Clamp Impulse Sealers are lightweight and easy to use anywhere. Available in 8", 12", and 16" seal lengths, the FKR-A-Series sealers are ideal for sealing polyethylene and laminated foils. Applications include sealing around oddly shaped products including drum or box liners for sealing around large objects.

Easy to Operate:

Operator simply places item to be sealed in between the jaws and squeezes the handle shut. An indicator light on the main housing unit signals the start and finish of the seal cycle. We recommend holding the jaws together for an additional 1-2 seconds after the light has turned off for the best quality seal. Heat cycle is controlled by a timer. The operator simply increases or decreases the heat as desired.

	FKR-200A	FKR-300A	FKR-400A
Sealing	Impulse	Impulse	Impulse
Seal Width	5mm	5mm	5mm
Power	110V / 200W	110V / 300W	110V / 400W
Seal Length	8"	12"	16"
Power Cord	Power Cord – 5ft Handle Cord – 7ft	Power Cord – 5ft Handle Cord – 7ft	Power Cord – 5ft Handle Cord – 7ft
Weight	20-lbs	20-lbs	20-lbs