

LONG HAND SEALER

FS-SERIES



Great value unit for sealing longer materials

- **Portable**
- **Aluminum construction**
- **No warm-up time needed**
- **Equipped with an electronic timer to control sealing time. Once the timer is set, sealer will provide a consistently flat seal**

More Details:

The FS-Series Long Hand Impulse Sealer series offers a longer sealing length for wider sealing applications. Sealers are available in 23.6", 31.5", or 39.5" with a 3 mm seal width.

Manufacturer's replacement kit includes two elements and one PTFE cover.

Easy to Operate: Set the timer, insert the bag between the sealing bar and the sealing platform. Press down on the seal bar and release the bar after the timer light turns off. We recommend that the user hold the sealing arm down for an additional second or two to ensure enough time for the bag to set and cool.

Option: Round elements are available for cut and seal applications.

When ordering, add the letters rnd to the model number

(Example: For a 23.6" hand sealer with a round cut wire, order model no. FS-600Hrnd.)

Specifications:

Model #	Seal Length	Seal Width	Power	Weight (lbs)
FS-600H	23.6"	2.8MM	110V / 780W	16
FS-800H	31.5"	2.8MM	110V / 1050W	18
FS-1000H	39.4"	2.8MM	110V / 1350W	20