

DIRECT HEAT SEALER FOOT OPERATED


THS-Series

- Easy to operate
- Seals a variety of thermoplastic materials
- Digital temperature controller
- Seal length: 8" (200mm), 12" (300mm), 16" (400mm)
- Seal width: 15mm
- Seal style: meshed or serrated (12" only)
- Option: sit down or stand up operation, PTFE coated jaws

Our THS-series direct heat sealers are equipped with a digital temperature controller. Available in 8", 12" and 16" lengths with a 15mm wide meshed seal. PTFE coated jaws are available in 8", 12" and 16" with model numbers, THS-200TC, THS-300TC and THS-400TC, respectively. We also offer a serrated seal style for the 12" unit (THS-300S).

Auto and foot-operated direct heat / constant heat sealers seal all types of thermoplastic packaging material, but are especially ideal for thicker material such as coated aluminum foil, Kraft paper, cellophane, mylar, coated PP. Please note: direct heat sealers cannot seal polyethylene. Depending on the model of the sealer, material up to 16" wide and 20 mil thick can be sealed. The meshed seal width is 15mm. Equipped with a digital temperature controller that accurately controls the temperature from 30°-550° F (0°-300° C). Both jaws are heated simultaneously resulting in better heat penetration to seal thicker material. Units also include an adjustable work table.

Easy to operate. Set the temperature on the temperature controller depending on the material to be sealed. Once the correct setting has been reached, consistent seals will be maintained automatically. Insert the material between the two sealing bars. Press down on the foot pedal and release.



Model #	Seal Length	Jaw Type	Watts	Weight (lbs)
THS-200	8"	Meshed	250W	38 / 9
THS-200TC	8"	Meshed, PTFE Coated	250W	38 / 9
THS-300	12"	Meshed	350W	43 / 9
THS-300TC	12"	Meshed, PTFE Coated	350W	43 / 9
THS-300S	12"	Serrated	350W	43 / 9
THS-400	16"	Meshed	420W	48 / 9
THS-400TC	16"	Meshed, PTFE Coated	420W	48 / 9

Sealer ships as two packages

RS-8

A 3-line mountable imprinter is an available option. The imprinter mounts on the upper jaw of the sealer. Seal and print in one single operation.

Ribbon colors available: black, red, & white

MFG 02.12.09.
EXP 00.12.09.
LOT 735 B QD

