

# TISH-SERIES HAND

*Impulse Sealers*

## TEW - the original hand impulse sealer


- **Plug-in electronic timer for variable control**
- **All metal construction**
- **No warm-up time**
- **Round wire option available for seal and cut**

TEW impulse hand sealers seal poly bags and other thermoplastic materials quickly and efficiently without any warm-up time. Depending on the model of the machine, material up to 16" wide and 10mil total thickness can be sealed. The sealers are equipped with a plug-in electronic timer which controls the different sealing times needed for the varying thicknesses of different materials. Available in 4", 8", 12", and 16" with a 2mm or 5mm seal width. Manufacturers' kit includes two elements and two PTFE covers.

**Cut and Seal Applications:** Round wire heating elements are available for cut and seal applications. There is no additional charge for the round cut wire. When ordering, add the letters rnd to the model number. (Example: 12" hand sealer with round cut wire – TISH-300rnd.)

### Easy to Operate:

Set the timer; insert the bag between the sealing bars, then press down and release. We recommend that the user hold the sealing arm down for an additional second or two to ensure enough time for the bag to set and cool.



Model #	Seal Length	Seal Width	Power	Weight (lbs)
TISH-100	4"	2MM	180W	5
TISH-105	4"	5MM	280W	5
TISH-200	8"	2MM	330W	7
TISH-205	8"	5MM	450W	9
TISH-300	12"	2MM	450W	11
TISH-305	12"	5MM	600W	13
TISH-400	16"	2MM	600W	16
TISH-405	16"	5MM	800W	18