

Instruction Manual	Manual de Instrucciones	Manuel d'instruction
Customer Service US: 1-800-645-2986	Servicio de atención al Cliente México: 01.800.681.6940	Service à la clientèle Canada: 888-645-2986

48" LED SHOP LIGHT - DOUBLE TUBES, 40W



Model 812410

⚠ WARNING

Please read entire manual carefully prior to installation and use. Failure to observe instructions could result in item damage, severe personal injury, and/or property damage.

- Installation and servicing should be done by a licensed electrician.
- This product must be installed in accordance with the National Electrical Code and all applicable local codes and safety standards.
- Any alteration or modification of this product is forbidden as it may cause product malfunction, property damage, personal injury or death.
- To avoid electric shock or component damage, unplug unit before installation or servicing.
- Be sure fixture temperature is cool enough before touching. Do not clean or maintain the fixture while unit is energized.
- Never use the cord for carrying, pulling or unplugging the power light. Grasp plug and pull to disconnect from outlet. Keep cord away from heat, oil, sharp edges or moving parts.
- Never attempt to plug in or operate light with defective or damaged wires, power cord, or power cord plug. All defective parts should be replaced immediately by qualified personnel.
- This product is for indoor use only.

SPECIFICATIONS


40W
Double Tube
120 Angle Beam, 5000K
4400lm, 110 lm/W
AC Input: 120-240V
Output: 72V
Product Dims: 48"L x 4.5"W x 1.8"H
50,000 Hours Rated Life
Power Coated Steel Housing
IP 20 Rated
ETL/cETL

- Keep this manual for future use.
- For additional questions or concerns, contact Global Industrial Customer Service at 1-800-645-2986 or visit www.globalindustrial.com.

INSTALLATION INSTRUCTIONS

⚠ WARNING

RISK OF ELECTRIC SHOCK. READ INSTRUCTIONS CAREFULLY BEFORE ATTEMPTING TO INSTALL THIS LIGHT. DISCONNECT MAIN POWER AT FUSE OR CIRCUIT BREAKER BEFORE INSTALLING OR SERVICING THE FIXTURE.




If mounting onto a solid hardwood surface, skip to step 3.

Using a 6mm drill bit, drill two holes in the desired mounting surface area. Note: Ensure mounting surface is adequate to support the weight of the light.




Using a hammer, tap the (2) 6mm wall anchors (provided) into the drilled holes.




Insert and twist the (2) 3.9mm hooks (provided) into the wall anchors until completely tight.


If mounting onto a solid hardwood surface, twist hooks directly into the surface (anchors are not required).




Slide the hanging cables through the holes on each end of the fixture, as seen in the illustration above.



If metal pull string is too high to reach, attach 3-ft. pullcord extension (included).



Hang the fixture by looping the (2) cables around the mounting hooks. Plug in power cord, and ensure the light turns on. The fixture is now installed.



Note: Up to 4 lights can be linked together.

Install additional fixtures by following the same instructions as above. Use the power cord to link two fixtures together, (see illustration above).