




H23110X

Blue Armor Full Body Harness

FEATURES

- Built in Relief Handles assist user to reach a gravity override seated position after a fall arrest
- 1¾ polyester WebAlert™ inspectable webbing
- Lightweight form fitting polyester back and waist pad with breathable compression interior
- Meets requirements of ANSI Z359.11



Blue Armor™

INSPECTABLE HARNESS



SPECIFICATIONS

Model No.	Size	D-Rings	D-Ring Material	Chest Connection	Leg Connection	Capacity	Approx. Weight	Compliance Standards
H231101	Small	Back; Hip	Steel	Pass Through	Pass Through	400 lbs (181 kg)	4.5 lbs (2.0 kg)	ANSI Z359.11 OSHA 29 CFR 1910 & 1926
H231102	Medium/Large	Back; Hip	Steel	Pass Through	Pass Through	400 lbs (181 kg)	4.5 lbs (2.0 kg)	ANSI Z359.11 OSHA 29 CFR 1910 & 1926
H231104	X-Large	Back; Hip	Steel	Pass Through	Pass Through	400 lbs (181 kg)	4.6 lbs (2.1 kg)	ANSI Z359.11 OSHA 29 CFR 1910 & 1926
H231105	XX-Large	Back; Hip	Steel	Pass Through	Pass Through	400 lbs (181 kg)	4.6 lbs (2.1 kg)	ANSI Z359.11 OSHA 29 CFR 1910 & 1926

⚠ WARNING: Compliant fall protection equipment must only be used as it was designed. Users MUST read and understand all user instructions provided with the product. Before using a fall arrest system, users must be trained in the safe use of the system, as required by OSHA 29 CFR 1910.30 and 1926.503, or local safety regulations. Misuse or failure to follow these warnings and instructions may result in injury or even death.

WORK SAFE! WORK SMART!

Technical Data Sheet