




A210400

- Meets the 5,000 pound tensile strength requirement when statically tested in accordance with the requirements of the ANSI Z359.1-2007 standard.
- Comes with twelve (12) 3 inch #12 Hex Head Screws
- Constructed with 1/8 inch plate steel
- Connection opening is 2 1/4 inches in diameter
- 32 Countersink holes (16 per side)
- May be mounted on the roof peak or mounted flat on one side of the roof.

Reusable Roof Anchor A210400



SPECIFICATIONS

Model No.	(A)	(B)	Depth	Capacity	Aprox. Weight	Compliance Standards
A210400	20 3/8 in (530 mm)	3 in (77 mm)	4 1/4 in (108 mm)	310 lb (141 kg)	2.5 lbs (1.1 kg)	ANSI Z359.1-07

⚠ WARNING: Compliant fall protection equipment must only be used as it was designed. Users MUST read and understand all user instructions provided with the product. Before using a fall arrest system, users must be trained in the safe use of the system, as required by OSHA 29 CFR 1910.66 and 1926.503, or local safety regulations. Misuse or failure to heed these warnings and instructions may result in injury or even death.

WORK SAFE! WORK SMART!

Technical Data Sheet