



LED WALL PACK LAMP



20W & 30W



50W - 120W



150W

PRODUCT FEATURES

- ADC12 Aluminum Heat Sink Housing
- Outdoor Powder Coating
- Bronze Finish
- Thick Custom Brackets to Seal and Protect from Elements
- EVA Gasket Mount which is Waterproof for Junction Box
- IP65 Rating - Suitable for Wet Locations
- 100-277 Voltage Rating
- 50,000 Hour Lifetime Rating
- Borosilicate Glass Lens (50W - 120W)
- High Light Transmittance PC, Anti-UV and Fire Resistance Lens (20W, 30W & 150W)
- Highly Conductive, Waterproof, Aging Resistance, Salt Mist Resistance Aluminum LED Board
- Tough Coated Wires / Quick-Connect Terminals
- Four (4) Threaded Apertures
- UL / DLC Certified
- 5-Year Limited Warranty

PRODUCT SPECIFICATIONS

| MODEL | POWER (W) | LUMENS (LM) | CCT (K) | DIMENSIONS (IN) | EFFICIENCY (lm/W) | DIMMING |
|-----------------------|-----------|-------------|---------|---------------------|-------------------|------------------|
| CLW4-205WMBR-S * | 20 | 2100 | 5000 | 6.81 x 10.95 x 5.08 | 100 | N / A |
| CLW4-305WMBR-S * | 30 | 3000 | 5000 | 6.81 x 10.95 x 5.08 | 100 | N / A |
| CLW4-505WMBR-2835 ** | 50 | 7100 | 5000 | 15.06 x 9.29 x 7.46 | 142 | N / A |
| CLW4-605WMBR-2835 ** | 60 | 8700 | 5000 | 15.06 x 9.29 x 7.46 | 145 | 0-10V / PWM / VR |
| CLW4-805WMBR-2835 ** | 80 | 11,600 | 5000 | 15.06 x 9.29 x 7.46 | 145 | 0-10V / PWM / VR |
| CLW4-1205WMBR-2835 ** | 120 | 17,100 | 5000 | 18.29 x 9.09 x 9.40 | 143 | 0-10V / PWM / VR |
| CLW4-1505WMBR | 150 | 19,350 | 5000 | 18.50 x 9.09 x 8.62 | 129 | 0-10V / PWM / VR |

* Dusk to Dawn Photocell Included
 ** DLC Premium Certified

