



15W w/
Knuckle Mount



30W w/
Knuckle Mount



50W w/
Knuckle Mount



50W w/
Yoke Mount

PRODUCT FEATURES

- ADC12 Aluminum Heat Sink Housing
- Outdoor Powder Coating
- Bronze Finish
- IP65 Rating - Suitable for Wet Locations
- 100-277 Voltage Rating
- UL Listed
- High Light Transmittance PC, Anti-UV and Fire Resistance Lens
- Highly Conductive, Waterproof, Aging Resistance, Salt Mist Resistance Aluminum LED Board
- Operating Temperature: -40°F to 104°F (-40°C to 40°C)
- 50,000 Hour Lifetime Rating
- 5-Year Limited Warranty

PRODUCT SPECIFICATIONS

MODEL	POWER (W)	LUMENS (LM)	CCT (K)	DIMENSIONS (IN)	EFFICIENCY (lm/W)	BEAM ANGLE / OPTIC TYPE	MOUNT
CLF4-15P53NBR	15	1800	3000	6.38 x 4.38 x 1.75	120	90° x 120°	KNUCKLE
CLF4-15P5KNBR	15	1800	5000	6.38 x 4.38 x 1.75	120	90° x 120°	KNUCKLE
CLF4-30P53NBR	30	3900	3000	6.88 x 9.0 x 2.0	130	90° x 120°	KNUCKLE
CLF4-30P5KNBR	30	3900	5000	6.88 x 9.0 x 2.0	130	90° x 120°	KNUCKLE
CLF4-50P5KNBR	50	6500	5000	8.75 x 10.0 x 2.0	130	90° x 120°	KNUCKLE
CLF4-50P5YKBR	50	6500	5000	9.38 x 9.75 x 2.00	130	90° x 120°	YOKE

