



100W - 150W



230W



300W

Mounts Sold Separately



STRAIGHT ARM



SLIP FITTER



TRUNNION



YOKE

### PRODUCT FEATURES

- ADC12 Aluminum Heat Sink Housing
- Outdoor Powder Coating
- Bronze Finish
- IP65 Rating - Suitable for Wet Locations
- Dimming: 0-10V/PWM/VR
- 50,000 Hour Lifetime Rating
- UL Listed
- 5-Year Limited Warranty
- High Light Transmittance PC, Anti-UV and Fire Resistance Lens
- Highly Conductive, Waterproof, Aging Resistance, Salt Mist Resistance Aluminum LED Board
- Operating Temperature: -40°F to 104°F (-40°C to 40°C)
- Mounts sold separately for 100W - 300W Flood Fixtures
  - Slip-Fitter - CLF4-SLIP FIT-Q (9.88 x 3.5 x 3.0)
  - Straight Arm - CLF4-STRAIGHT ARM-Q (7.13 x 6.13 x 3.5)
  - Trunnion - CLF4-TRUNNION-Q (5.75 x 6.0 x 2.0)
  - Yoke - CLF4-YOKE-Q-80W-230W (13.38 x 10.13 x 1.75)

### PRODUCT SPECIFICATIONS

MODEL	POWER (W)	LUMENS (LM)	CCT (K)	DIMENSIONS (IN)	EFFICIENCY (lm/W)	BEAM ANGLE / OPTIC TYPE	VOLTAGE (V)
CLF4-100QP5YYBR	100	13,500	5000	12.3 x 12.6 x 2.6	135	TYPE III	100 - 277
CLF4-150QP5YYBR	150	20,250	5000	12.3 x 12.6 x 2.6	135	TYPE III	100 - 277
CLF4-230QP5YYBR	230	32,200	5000	14.1 x 12.6 x 2.6	140	TYPE III	100 - 277
CLF4-300QPH5YYBR	300	42,000	5000	17.9 x 12.6 x 2.8	140	TYPE III	277 - 480

