ROTARY AIR/HYDRAULIC SCISSOR TABLE, AHLT-3060-3-43



STANDARD FEATURES:

SCISSOR TABLE MODEL NUMBER IS AHLT-3060-3-43
PLATFORM WIDTH IS 30 INCHES
PLATFORM LENGTH IS 60 INCHES
PLATFORM RAISED HEIGHT IS 43 INCHES
PLATFORM LOWERED HEIGHT IS 7 INCHES
TABLE CAPACITY (EVENLY DISTRIBUTED LOAD) IS 3,000 LBS.
CONNECTION: 1/2" NPT AIR LINE
HINGED MAINTENANCE PROPS, PNEUMATIC UPPER TRAVEL LIMIT SWITCH,
TOE GUARDS, & INTERNAL BRASS VELOCITY FUSE STANDARD

SPECIAL FEATURES:

NONE

Deck tolerances +/- 1/2"
Table height tolerances +/- 1/2"
Deck Flatness ± 1/4"

***ROTARY-######## ROTARY AIR/OIL POWER UNIT,
AIR REQUIREMENT 80 cfm @ 80 psi
REQUIRES A FILTER/REGULATOR/LUBRICATOR, FRL
WARRANTY IS VOID IF NOT USED
3/4" dia AIR SUPPLY @ 50 ft MAX
DECIBEL LEVEL 100dB @ 6 ft, 90dB @ 10 ft

PLEASE CIRCLE SPECIFICATIONS:

POWER	~~AC~~	~~DC (12V)~~	AIR/OIL	
MOTOR VOLTAGE	~~115~~	~~208~~	~~230~~	~~460~~
DEDICATED CIRCUIT REQUIRED				
MOTOR PHASE	~~SINGLE~~	~~THREE~~		
CONTROL	HAND	~~*FOOT~~		
POWER UNIT LOCATION	INTERNAL	~~*EXTERNAL~~		

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN & DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT & INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS & STANDARDS.

ALL SPECIAL UNITS ARE NON-RETURNABLE

[ ] As drawn [ ] As marked

Signed:_____ Date: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

Any additions, deletions or onissions must be corrected on this drawing, as this drawing will be considered all inclusive.

All graphics provided are for refereneceonly. If certain dinensions are critical please verify those dimensions with your salesperson

DISTRIBUTOR'S NAME: VESTIL MFG

P.O.#: _

W.O.#: _

DRAWN BY: _

DATE: _

SALES: _

REFERENCE: _

SCALE: _

DRWG./FILE NAME: 24-007-051-101

QUOTED LEADTIME: _

QUOTE #: _