7000CJ

JEWELRY STEAM CLEANER

The 7000CJ produces up to 65 PSI of steam pressure and reaches temperatures up to 221˚F at the tip. It's ideally suited for use in jewelry stores and work- rooms for cleaning away left over wax, plaster waste and other debris, and for polishing the final product.

Steam deodorizes and sanitizes with heat and moisture and since the only ingredient required for the 7000CJ is water, cleaning has never been safer, healthier or more environmentally friendly.

SPECIFICATIONS

ELECTRICAL	120V	
WATER CAPACITY	2.37 GAL	9L
OPERATING PRESSURE	Up to 65 PSI	4.5 BAR
STEAM TEMPERATURE	221°F	105°C
ELEMENTS	2 - 1,200W each (1 spare)	
POWER CONSUMPTION	10 amps	
TANK CONSTRUCTION	Stainless steel	
LOW WATER INDICATOR	Standard	
NET WEIGHT	30.35 lb	13.75 kg
SHIPPING WEIGHT	33.9 lb	15.37 kg
PRODUCT DIMENSIONS	12.25" x 14.25" x 20.5"	31 x 36 x 52 cm
SHIPPING DIMENSIONS	16" x 14.75" x 24.25"	40.5 x 37.5 x 61.5 cm
ELECTRICAL APPROVAL	cETLus	
WARRANTY	Limited 1 year, 2 year boiler tank	

THE POWER OF STEAM

4 SAFETY SYSTEMS

STAINLESS STEEL ENCLOSURE

PRESSURE GAUGE

MADE IN ITALY

BLOW DOWN VALVE

BOILER TANK 2 YEAR WARRANTY

THERMOSTAT RESET

4.5 BAR PRESSURE

RELIABLE

7000CJ

JEWELRY STEAM CLEANER

RELIABLE