DEWALT

20V MAX* BRUSHLESS

DCG410B

20V MAX* XR® 4-1/2 IN. - 5 IN. ANGLE GRINDER (TOOL ONLY)

- PART OF OUR MOST POWERFUL LINE OF 20V MAX* ANGLE GRINDERS**
- ANTI-ROTATION SYSTEM: Equipped with PERFORM & PROTECT™ features
- POWERFUL PERFORMANCE: Up to 1,590 MWO and 9,000 RPM (no load)
- SIMPLIFY ASSET MANAGEMENT: TOOL CONNECT™ CHIP READY™ system (chip sold separately)



*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

**Rated MWO.

XR®

VARIABLE SPEED	SWITCH TYPE	TOOL WEIGHT (TOOL ONLY)
NO	PADDLE SWITCH	3.92 LBS

Includes: (1) DCG410 XR® Angle Grinder, (1) 5 in. (125 mm) Type 27 Guard, (1) Side Handle, (1) Wrench, (1) Inner and Outer flange

© 2024 DEWALT

ICDCD410BFT