ABS American BioTech Supply

Premier Hydrocarbon Manual Defrost Freezers

FEATURES

- 14 and 20 Cu. Ft. capacity
- Microprocessor temperature controller
- Digital temperature display
- Remote alarm contacts
- Sample simulated temperature display
- Audible and visual high and low temp alarms
- Adjustable operating temp range: -15°C to -25°C
- Six fixed shelves
- Keyed door lock
- Natural HC Refrigerant R290
- Probe access port (3/8")

ABT-HC-MFP-20

ABT-HC-MFP-14

ENERGY STAR

Environmentally friendly, natural hydrocarbon (HC) refrigerants which vastly reduce global-warming potential while meeting new EPA/SNAP mandates.

125 Varnfield Drive
Summerville, SC 29483

800-648-4041

americanbiotechsupply.com

The Premier Hydrocarbon Manual Defrost Freezers take a large step forward in performance from past solid door general purpose units; offering a digital temperature display and alarm module coupled with a microprocessor temperature controller.

ABS American BioTech Supply

Front View
ABT-HC-MFP-20



Front View
ABT-HC-MFP-14



ABT-HC-MFP-20
Interior

Model	Ft³	Defrost	Door	Int Door	Shelves	W"	D"	H"	RL	H.P.	Amps
ABS-HC-MFP-14	14	Manual	1	0	6 Fixed	23 ⅝	24 ⅜	73	R290	½	1.96
ABS-HC-MFP-20	20	Manual	1	0	6 Fixed	30 ¾	28 ½	74 ⅝	R290	½	1.96

Specifications are subject to change

The Hydrocarbon Manual Defrost freezer easily maintains air temperatures below -20°C, throughout the chamber.



EMPTY CHAMBER, TEMP SET POINT: -24°C

v1.0_02182019