Sa	afety Data Sheet (SDS) 908480 Triple Play	У	10/13/2016			
1.	Identification Product Identity: Triple Play Recommended Use: Water-based low foam carpet cleaner Producer / Distributor Multi-Clean 600 Cardigan Road Shoreview, MN 55126		38 Multi-Clean®			
	Telephone Number for Information: 651-481-1900 Emergency Telephone Number: 800-255-3924					
2.	Hazard Identification Classification: Health Class Eye Irritant Category 2 Label Symbols	Physical Class	Environment Class			
	Signal Word Warning Hazard Statements: Causes eye irritation. Precautionary Statements: Wash hands thoroughly after handling. IF IN EYES: Rinse cautiously with water for several minutes. F If eye irritation persists: Get medical attention.	Remove contact lenses if	present and easy to do. Continue rinsing.			
3.	Composition/Information on Ingredients Ingredient Dipropylene Glycol Methyl Ether Diethylene Glycol Monobutyl Ether Surfactant Blend Bacterial Spore Blend Water	CAS Number 34590-94-8 112-34-5 Proprietary Proprietary 7732-18-5	Percent by Weight 1 - 5 1 - 5 1 - 5 1 - 5 1 - 5 60 - 100			
I .	 First-Aid Measures: Ingestion: If Swallowed: Drink water in large amounts and call a physician immediately. Never give anything by mouth to an unconscious person. Eye Contact: Flush eyes with running water for at least 15 minutes. If irritation persists, obtain medical attention. Skin Contact: Flush with cool water. Remove and wash contaminated clothing before reuse. Inhalation: Move to fresh air. 					
5.	Fire Fighting Measures: Suitable Extinguishing Media: Not Applicable Special Fire Fighting Procedures: Not Applicable Unusual Fire and Explosion Hazards Not Applicable					
5.	Accidental Release Measures: Dike and contain spill with inert material (sand, earth, etc.). Collect spill with a mop, absorbent material (example: floor-dry) or vacuum. Thoroughly rinse affected area with water.					
r.	Handling and Storage: Handling: Keep from freezing. Keep out of reach of children Storage: Normal care for storage.					

8.	Exposure Controls / Personal Protection: Exposure Limits Ingredients Dipropylene Glycol Methyl Ether Diethylene Glycol Monobutyl Ether Exposure Controls Engineering Controls: Normal good ventilation is sufficient Personal Protective Equipment: Eye Protection: Approved Safety Goggles or Glasses Skin Protection: Chemical Resistant Rubber Gloves Respiratory Protection: Not required, Avoid breathing spra	CAS Number 34590-94-8 y mist	Osha PEL 100 ppm	ACGIH TLV 100 ppm		
9.	Physical and Chemical Properties: Physical State: Liquid Appearance: Turquoise Odor: Fresh & Clean Solubility: Complete Evaporation Rate: NA Vapor Pressure (MM HG): NA Vapor Density (Air = 1): NA	<pre>pH: 9-10 Specific Gravity (H2O = 1): 1.004 Flammability: None Flash Point: None Boiling Point: > 212° F (100°C) %volatile: > 85%</pre>				
10.	Stability and Reactivity: Chemical Stability: Stability: Stability of Hazardous Reactions: None are known Incompatability (Materials to Avoid): None are known Hazardous Decomposition or By-products: None Hazardous Polymerization: Will not Occur Conditions to Avoid:					
11.	Toxicological Information: Signs and Symptoms of Overexposure: May cause irritation to Eyes on direct contact Acute Effects: Eye Contact: May cause irritation on contact Skin Contact: May cause irritation on prolonged or repeated contact Inhalation: None Known Ingestion: May be harmful if swallowed Target Organ Effects: None are known Chronic Effects: None are known Acute Toxicity Values: Oral LD 50 > 5000 mg/kg Dermal LD 50 > 5000 mg/kg Inhalation (Vapor) LC 50 > 50 mg/l					
12.	Ecological Information: Persistence and Degradability: Product is Readily Biodegrad Bio Accumulative Potential: Not Available Mobility in Soil: Not Available Aquatic Toxicity: Not Available	able				
13.	Disposal Considerations: Material that cannot be used during normal use should be disposed of in accordance with all applicable local, state and federal regulations. Waste from normal cleaning procedures may be disposed of in a sanitary sewer depending on the materials and/or contaminants being cleaned as well as local, state and federal sewer regulations.					

14. Transportation Information:

UN Number: None Shipping Name: Cleaning Compound, Liquid Transport Hazard Class: None Packing Group: None Marine Pollutant: NO

Safety Data Sheet (SDS)

908480 Triple Play

15. Regulatory Information:

TSCA Status: All ingredients listed Clean Water Act: None of the chemicals in this product are listed under the CWA Clean Air Act: None of the chemicals in this product are listed under the CAA CERCLA Reportable Quantity: None SARA Title III Information: None Listed Section 302 Extremely Hazardous Chemicals: Section 311 / 312 Hazard Category: Immediate Health Section 313 Toxic Chemicals: None Listed State Regulations: None

International Regulations: WHMIS Controlled Product Hazard Class: D2B

16. **Other Information:**

Prepared By: Eric Scholl Telephone Number: 651-481-1900 Revision Date: 10/13/2016 Supersedes: 10/29/2014 This SDS applies to the following Part Numbers 902163

902167

The information contained herein is based on data considered accurate; however no warranty is expressed or implied regarding the accuracy of this data or the results to be obtained from the use thereof. The company assumes no responsibility for personal injury or property damage to vendees, users, or third parties caused by the material. Such vendees or users assume all risks associated with the use of the material.



