

# PORTABLE SINKS

CV-PHS-1, 2, 3, 4

Project: \_\_\_\_\_

Item #: \_\_\_\_\_

Quantity: \_\_\_\_\_



CV-PHS-1



CV-PHS-1



CV-PHS-4

For the large community outdoor function, when hand-washing is a must! Shipped fully assembled, complete with removable fresh and waste water tanks, 12 foot cord, standard wall plug and city water and drain hookups. Available in eight convenient configurations.

Now includes pump-saver foot switch to eliminate pump burn out, allowing the operator to use the foot pedal to turn the faucet on/off.

## SPECIFICATIONS

- Stainless steel construction
- Lockable access Door
- 120 Volt water heater 2 Imp. Gallons
- 120 Volt water pump
- PHS available with 1,2, or 3 sink compartments
- Available in a compact (CV-PHS-4) cabinet version
- 2 x 20 litre (5 gallon) removable fresh water tanks
- 2 X 30 litre (7.5 gallon) removable waste water tanks
- Backsplash w/ soap & towel dispensers
- 12 foot cord with standard wall plug
- City water and drain hookups
- Ready to use: ships completely assembled and crated
- All units are NSF, CSA, UL or equal approved
- 1 year parts and labour warranty

## Certifications



**SPECIFICATIONS**



Model	<b>CV-PHS-1</b> <b>CV-PHS-1C (COLD)</b>	<b>CV-PHS-2</b> <b>CV-PHS-2C (COLD)</b>	<b>CV-PHS-3</b> <b>CV-PHS-3C (COLD)</b>	<b>CV-PHS-4</b> <b>CV-PHS-4C (COLD)</b>
<b>Sink Bowl Size</b>	14"Lx 12"Wx 6"H	12"Lx 6"Wx 5"H	12"Lx 6"Wx 5"H	14"Lx 12"Wx 6"H
<b>Sinks</b>	1	2	3	1
<b>Actual Weight (lbs)</b>	160	160	160	140
<b>Shipping Weight (lbs)</b>	218	218	218	190
<b>Fresh water capacity</b>	2 x 5 Gallon	2 x 5 Gallon	2 x 5 Gallon	1 x 5 Gallon
<b>Waste water capacity</b>	2 x 7.5 Gallon	2 x 7.5 Gallon	2 x 7.5 Gallon	1 x 7.5 Gallon
<b>Cabinet Size</b>	34.375"W x 25.25"D x 38.25" H	34.375" W x 25.25" D x 38.25" H	34.375"W x 25.25" D x 38.25" H	24" W x 25.25" D x 38.25" H

