

# CLUB GRILLS

CCB- 60, 72

Project: \_\_\_\_\_

Item #: \_\_\_\_\_

Quantity: \_\_\_\_\_



Our CCB line allows for customers in a buffet line to be served directly from the grill. By incorporating two 30 Lb. horizontal propane tanks, the grill is easier to move and eliminates a propane tripping hazard; all while improving the overall appearance. Heavy duty brackets secure the tanks in place and are designed to make removal/placement of the propane tanks an extremely simple process.

Our grill bodies, legs, cooking grates, burners, under shelves, radiants, water pans, fasteners, pilot tubes are all constructed of 304 series stainless steel for durability and ease of cleaning. Compared to units made of metal or 430 stainless steel, our units are built to last.

15,000 BTUH stainless steel burners are placed every 5.75" to ensure the most even heat pattern possible. These units heat up to cooking temperature within 5 minutes. Our stainless steel burners and cooking grills carry a 10 year and lifetime warranty, respectively.

The CCB model is available in liquid propane (LP) only. All LP models include a two stage regulator(s) and hose(s) and two 30 Lb. horizontal propane tanks.

## SPECIFICATIONS

- Gas grill constructed of 304 stainless steel including grids, burners and all fasteners
- 15,000 BTUH stainless steel burners
- Two 14" wheels and two total lock casters
- Ready to use: ships completely assembled on a skid
- Heavy duty brackets secure 30 Lb. tanks on the undershelf
- Storage shelf and angled legs for rock solid durability
- Includes water pans with drain ports to ease cleaning and help eliminate grease fires from occurring
- 16 ga stainless steel radiants that remain in place during transportation and cleaning
- c ETL us, ETL Sanitation listed, Conforms to ANSI Z83.11/CSA 1.8 and NSF Standard 4

## More Standard Features

- Unibody design for lighter weight and added strength
- Stainless steel pilot burner tube system
- Two stage regulator(s) and hose(s)
- Factory technician tested prior to shipping
- 1 year parts and labor limited warranty
- Lifetime warranty on body and cooking grids and 10 years on burners

## Options/Accessories

- |               |                     |
|---------------|---------------------|
| Roll Dome     | Adjustable Bun Rack |
| Griddle Plate | Steam Pan Adapter   |
| End Shelf     | Front Shelf         |
| Side Burner   | Rotisserie          |
| Wind Guard    | Smoker Box          |
| BBQ Cover     | Charcoal Tray       |


## Certifications



**SPECIFICATIONS**



Model	CCB-60	CCB-72
Number of Burners	8	10
BTUH	129,000	159,000
Actual Weight (lbs)	286	334
Shipping Weight (lbs)	348	422
Gas Connections (LP)*	2	2
Cooking Surface	58" x 21"	70" x 21"
Overall Dimensions	69" L x 28" D x 36" H	81" L x 28" D x 36" H



CCB	"X"
60	69"
72	81"

