

EZ-Breeze HAF Basket Fan

RECIRCULATION FANS

J&D Manufacturing's EZ-Breeze HAF (Horizontal Air Flow) Fan is a high-efficiency air circulator that effectively cools people, plants, animals and industrial equipment. The EZ-Breeze reduces condensation, dries animal litter and bedding, controls insects, and creates a uniform temperature throughout your building to reduce heating costs.

Features

- Available in 12", 16", 20" and 24"
- Includes corrosion resistant hot dip galvanized mounting bracket with u-bolts and nuts
- Aluminum propeller designed to reduce ambient noise levels while maintaining maximum circulation requirements
- Efficient variable speed motors *(requires separate variable speed control to adjust fan speed)*
- Corrosion resistant, white powder coated fan guards meet OSHA 1910.212(a)(5) requirements for installation at any height
- Fan ships completely assembled and ready for installation
- Attached 10' cord with 3-prong plug pre-wired for 115 volts
- Totally enclosed, maintenance-free, direct drive high-efficiency motors have completely sealed ball bearings, are UL/CUL recognized, and are covered by a **Two Year Warranty**
- For additional cooling, use with our misting/fogging product line



VRSBR736-U
VRSBR8-U
VRSBR5-U



No electrician needed!
**Hang it up
Plug it in**

**Guards Meet
OSHA
Requirements**



Part#~	Size	Ph	Spd	Thrust CFM	Thrust CFM/Watt	Drive	Prop	Included Bracket
Single Phase								
VDB12G	12"	1	1/Var^	960	8.3	Direct	3-Alm	VRSBR736-U
VDB16G	16"	1	1/Var^	1,710	12.7	Direct	3-Alm	VRSBR736-U
VDB20G	20"	1	1/Var^	1,410	14.9	Direct	3-Alm	VRSBR8-U
VDB203G	20"	1	1	3,390	11.9	Direct	3-Alm	VRSBR8-U
* VDB24G	24"	1	1	3,500	12.3	Direct	3-Glv	VRSBR5-U
VDB242G	24"	1	1	5,020	12.3	Direct	3-Alm	VRSBR5-U

* Best sellers/recommended models

~ These units come pre-wired for 115 Volts *(electrician may rewire for 230 Volts)*

^ Variable speed fans require separate variable speed control to adjust fan speed

Bold red text is data based on testing performed by an accredited lab using ANSI/AMCA Standard 230-12

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov/product.