


# Storm Series of Fans

## 55" Fiberglass Exhaust Fans



**⚠ WARNING:** This product can expose you to chemicals including chromium, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov/product](http://www.P65Warnings.ca.gov/product).

# Storm

## Belt Drive 55" Fiberglass Exhaust Fan



### Motor


- High-efficiency
- Totally enclosed
- 1 HP, 1½ HP or 2 HP
- Covered by a **2 Year Warranty**

### Belt Tensioner

- Automotive style
- Toolless belt changing

### Prop Options

- High-performance cast aluminum prop with **Lifetime Warranty**
- Galvanized prop with **1 Year Warranty**



**Shown with shutter removed**  
(Never permit power to fan with shutter removed)

### Shaft Bearings

- Pre-lubricated
- Featuring an eccentric locking collar with set screw
- Permanently sealed and rubber mounted for smooth operation
- Covered by a **3 Year Warranty**



Part #	Sz	Ph	Spd	@ 0.10" SP		Drive	Prop
				CFM	Watt		
Single Phase							
Aluminum Shutter							
VSA55G3C11E-SL	55"	1	1	21,189	23.4	Belt	3-Glv
VSA55A3C151-SL	55"	1	1	24,056	19.0	Belt	3-CA
VSA55G3C151-SL	55"	1	1	23,985	21.8	Belt	3-Glv
* VSA55A3C21-SL	55"	1	1	28,347	13.8	Belt	3-CA
VSA55G3C21-SL	55"	1	1	27,546	16.1	Belt	3-Glv
Poly Shutter							
VSP55G3C11E-SL	55"	1	1	19,799	21.3	Belt	3-Glv
* VSP55A3C151-SL	55"	1	1	22,348	17.6	Belt	3-CA
VSP55G3C151-SL	55"	1	1	22,903	20.4	Belt	3-Glv
VSP55A3C21-SL	55"	1	1	27,087	13.2	Belt	3-CA
VSP55G3C21-SL	55"	1	1	26,601	15.2	Belt	3-Glv
Three Phase							
Aluminum Shutter							
VSA55A3C153-SL	55"	3	1	23,774	19.3	Belt	3-CA
VSA55G3C153E-SL	55"	3	1	23,844	22.0	Belt	3-Glv
VSA55A3C23-SL	55"	3	1	31,060	13.6	Belt	3-CA
VSA55A3C23E-SL	55"	3	1	28,515	15.4	Belt	3-CA
* VSA55G3C23-SL	55"	3	1	31,402	16.0	Belt	3-Glv
VSA55G3C23E-SL	55"	3	1	26,411	20.6	Belt	3-Glv
Poly Shutter							
VSP55A3C153-SL	55"	3	1	22,624	17.9	Belt	3-CA
VSP55G3C153E-SL	55"	3	1	22,746	20.5	Belt	3-Glv
* VSP55A3C23-SL	55"	3	1	30,058	12.8	Belt	3-CA
VSP55A3C23E-SL	55"	3	1	27,250	14.7	Belt	3-CA
VSP55G3C23-SL	55"	3	1	30,471	15.1	Belt	3-Glv
VSP55G3C23E-SL	55"	3	1	25,475	19.5	Belt	3-Glv

### Non Slant Wall Versions

Remove "-SL" at end of part # - Example: VSSP55A3C23

**Black Versions** (requires extended lead time)

Add "-B" to end of part # - Example: VSSP55A3C23-SL-B

\* Best sellers/recommended models

**Bold red text is data based on testing performed by an accredited lab using ANSI/AMCA 210-07 standard.**

**⚠ WARNING:** This product can expose you to chemicals including chromium, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov/product](http://www.P65Warnings.ca.gov/product).