PORTACOOL



APEX 4000

PEAK COOLING, INTELLIGENT CONTROL

Introducing the Portacool Apex[™] 4000: the perfect blend of innovation and simplicity to keep you cool wherever you go. Operating at a volume comparable to an electric toothbrush, this unit is designed to cool spaces up to 4000 square feet, emits just 62 dB. It offers extensive cooling for expansive areas with minimal noise and is ideal for industrial, commercial, and large event venues. The Apex 4000 provides a refreshing breeze that reaches up to 50 ft. while maintaining a comfortable sound level.

- 1. Smart, Connected Cooling
- 2. Quiet, Efficient, and Far-Reaching
- 3. Rugged, Portable, and Smartly Designed



POWERED BY COOLSYNC[™] TECHNOLOGY.

The ultimate evaporative coolers are here. Connectivity powered by CoolSync[™] Technology. Sync your cooler to your smartphone and take total control from anywhere.

- Easily adjust fan speeds
- Control multiple units simultaneously
- Schedule run-times in advance
- Set a timer for the cooling duration

Lifetime warranty on all molded housings. 3yr. *Limited warranty on motor and electrical components.



www.portacool.com

PORTACOOL

POWERFUL & EFFICIENT COOLING:

This chart illustrates the remarkable cooling capabilities of the Apex Series high-velocity evaporative coolers. The Apex 4000, designed for cooling spaces up to 4000 square feet, creates a refreshing breeze that extends up to 50 feet.



APEX 4000

- Extended Cooling Reach -Our high-velocity cooler delivers a refreshing breeze up to 50 ft. away.
- Whisper Quiet Performance -The unique fan blade and motor design combination minimizes noise, creating a tranquil environment while delivering powerful cooling.
- Simplify Your Space New housing design keeps cords and connections neatly tucked away at the back for a cleaner, smarter cooler experience.
- Unmatched Portability -Built-in handles and lightweight housing ensure easy transportation over any terrain.



MODEL NUMBER	OPTIMAL COOLING (Sq. Ft.)	VELOCITY (Mph)	AIR FLOW REACH (Ft.)	NOISE (dB)	WATER RESERVOIR (Gallons)	PRODUCT WEIGHT (Without Water)	AIRFLOW (CFM'S)	AMP'S	DIMENSIONS (In.)
PACA40001A1	UP TO 4000	25	50	62	55	220	13250	9.0	(HEIGHT) 77 (DEPTH) 33 (WIDTH) 63

Lifetime warranty on all molded housings.

3yr. *Limited warranty on motor and electrical components.

www.portacool.com

Portacool parts and accessories are available online at portacool.com or through your local distributor or retail location.



PARMKTLT507 3/04/24