PORTACOOL



APEX 500

PEAK COOLING, INTELLIGENT CONTROL

Discover the Portacool Apex™ 500, where innovation and simplicity join to help you stay cool in every space. As guiet as a library at 53 dB, this cooler is perfect for cooling an area of 500 square feet, making it ideal for places such as workshops, auto shops, and outdoor decks. It delivers a robust 55 ft. breeze, ensuring cool comfort without disrupting the peace.

- 1. Smart, Connected Cooling
- 2. Quiet, Efficient, and Far-Reaching
- 3. Rugged, Portable, and Smartly Designed





POWERED BY COOLSYNC™ TECHNOLOGY.

The ultimate evaporative coolers are here. Connectivity powered by CoolSync™ Technology. Sync your cooler to your smartphone and take total control from anywhere.

- Easily adjust fan speeds
- Control multiple units simultaneously
- Schedule run-times in advance
- Set a timer for the cooling duration

Lifetime warranty on all molded housings.

3yr. *Limited warranty on motor and electrical components.



PORTACOOL

POWERFUL & EFFICIENT COOLING:

This chart illustrates the remarkable cooling capabilities of the Apex Series high-velocity evaporative coolers. The Apex 500, designed for cooling spaces up to 500 square feet, creates a refreshing breeze that extends up to 55 feet.



Digital display

CoolSync™_

technology

Improved 8"

edge-coat media

with new water_

Portacool

technology

Frontline -

airflow inlet

APEX 500

- **Space Optimization -**Achieve maximum cooling without sacrificing space. Our slimmer profile and new front intake allows you to place your Portacool evaporative cooler against any wall.
- **Extended Cooling Reach -**Our high-velocity cooler delivers a refreshing breeze up to 55 ft. away.
- **Digital Louver Control -**The oscillating louvers allow customized airflow to maximize your cooling coverage.
- Whisper Ouiet Performance -The centrifugal blower design and motor combination reduce noise, creating a tranquil cooling environment.

SLIMMER PROFILE



| MODEL NUMBER | OPTIMAL COOLING (Sq. Ft.) | VELOCITY (Mph) | | NOISE (dB) | WATER RESERVOIR (Gallons) | PRODUCT WEIGHT (Without Water) | AIRFLOW (CFM's) | AMP'S | DIMENSIONS (In.) |
|--------------|------------------------------|-------------------|----|---------------|------------------------------|-----------------------------------|--------------------|-------|-------------------------------------------|
| PACA05001A1 | UP TO 500 | 40 | 55 | 53 | 13 | 70 | 800 | 2.4 | (HEIGHT) 46 (DEPTH) 19.5 (WIDTH) 22 |

Lifetime warranty on all molded housings.

3yr. *Limited warranty on motor and electrical components.



www.portacool.com

Portacool parts and accessories are available online at portacool.com or through your local distributor or retail location.

PARMKTLT503 3/04/24