

Touchless. Hygienic. Sustainable.



XLERATOR®

Original. Patented.
Still The Best.

ThinAir®

Surface-Mounted.
ADA-Compliant.

XLERATOReco®

High-Speed. No Heat.
500 Watts.

INDUSTRY LEADING 7-YEAR WARRANTY.

XLERATOR & XLERATOReco

OPTIONAL HEPA FILTRATION SYSTEM

REMOVES 99.999% OF VIRUSES FROM THE AIRSTREAM¹

¹Based on testing performed by LMS Technologies, April 2020.

BENEFITS OF EXCEL'S HIGH-SPEED, ENERGY-EFFICIENT HAND DRYERS

- ✓ 95% Cost Savings vs. Paper Towels
- ✓ A Hygienic Hand Drying Solution
- ✓ 5-Year Limited Warranty for ThinAir Models
- ✓ Washable Pre-Filter
- ✓ The First EPD-Certified Hand Dryers
- ✓ Made In USA® Certified
- ✓ Qualifies for the Most LEED® Credits of Any Hand Dryer
- ✓ Reduces Carbon Footprint of Hand Drying by 50-75%
- ✓ 80% Less Energy Than Conventional Hand Dryers
- ✓ The First HPD-Certified Hand Dryers



XLERATOR



XLERATOReco



ThinAir

ORIGINAL. PATENTED. STILL THE BEST.

- ✓ Virtually Maintenance-Free
- ✓ Over 15 Years of Proven Performance
- ✓ Optional HEPA Filtration System

HIGH-SPEED. NO HEAT. 500 WATTS.


- ✓ Innovative No Heat Technology
- ✓ Can Install Multiple Units on One Circuit
- ✓ Optional HEPA Filtration System

SURFACE-MOUNTED. ADA-COMPLIANT.

- ✓ Now Available With Optional HEPA Filtration System
- ✓ New Painted and Custom Cover Options
- ✓ Meets 4" ADA Protrusion Guidelines

| FEATURES | XLERATOR | XLERATOReco | ThinAir |
|---|--|--|--|
| LIST PRICE | \$650-\$920 | \$620-\$890 | \$500-\$750 |
| DRY TIME | 8 Seconds* | 10 Seconds* | 14 Seconds* |
| WARRANTY | 7-Year | 7-Year | 5-Year |
| ENERGY USE | 3.7 Wh* | 1.7 Wh* | 3.7 Wh* |
| ADJUSTABLE SOUND | 65 - 75 dB | 65 - 75 dB | 69 - 73 dB |
| WATTS | 1490W (Heat On), 425W (Heat Off) | 425W-530W | 950W (Heat On), 300W (Heat Off) |
| VOLTS / AMPS | 110-120V 11.3-12.2A 60Hz 208-277V 5.6-6.2A 60Hz 230V 6.1A 50Hz | 110-120V 4.3-4.5A 60Hz 208-277V 2-2.2A 60Hz 230V 2.2A 50Hz | 110-120V 7.2-7.8A 60Hz 208-277V 3.6-4A 60Hz 230V 3.9A 50Hz |
| CUSTOM COVERS | ✓ | ✓ | ✓ |
| FILTERS | Washable Pre-Filter (Optional HEPA Filtration System) | Washable Pre-Filter (Optional HEPA Filtration System) | Washable Pre-Filter (Optional HEPA Filtration System) |
| MADE IN USA | ✓ | ✓ | ✓ |
| EPD, HPD, AND BUILDINGGREEN APPROVED | ✓ | ✓ | ✓ |
| ADA-COMPLIANT | With Optional ADA Recess Kit #40502 | With Optional ADA Recess Kit #40502 | ✓ |
| LEED CREDITS | ✓ | ✓ | ✓ |

CUSTOM COVERS



ACCESSORIES

- ✓ 1.1" Noise Reduction Nozzle
- ✓ HEPA Filtration System Removes 99.999% of Viruses from Airstream
- ✓ ADA-Compliant Recess Kit
- ✓ Antimicrobial Wall Guards
- ✓ XChanger® Towel Dispenser Retrofit Kit



Global Industrial
www.globalindustrial.com
(800) 645-1232

*Dry time and energy use testing performed by SGS International on standard XLERATOR/XLERATOReco Hand Dryers with 0.8" nozzle/standard ThinAir Hand Dryers to 0.25g or less of residual moisture, pursuant to the UL Environment Global Product Category Rules (PCR) for Hand Dryers.



TIME TO THROW IN THE TOWEL®

EXCEL DRYER INC • 1.800.255.9235 • EXCELDRYER.COM

FEB 2021