

Revelation III

The Revelation III professional-grade microscope is a best-seller into physician clinics, as well as universities and medical schools. The Revelation III comes with LED illumination for daylight color, low heat, low power consumption, and super-long bulb life (30,000 hours). Equipped for performance, its features include titanium-finished DIN achromatic or DIN Plan optics and a 30-year anti-fungal coating. The Revelation III is the choice for superior performance at a great value!



HEAD

Binocular (Seidentopf)
Inclined 30°, rotates 360°
Diopter adjustment
10X/18 wide field eyepieces (10X/20HP available)
Monocular, trinocular, dual binocular and
45° sliding heads available
Interpupillary distance range:
Binoc head: 48-75mm
Trinoc head: 55-75mm

NOSEPIECE

Quadruple forward-facing nosepiece
Multiple ball bearing mounted

OBJECTIVES

DIN Achromatic or DIN Plan
30 year anti-fungal coating
4X, 10X, 40X, 100XR (oil)
Parfocal, parcentric, color-coded

STAGE

Mechanical stage (140mm x 130mm)
Coaxial drive controls
Range of traverse is 78mm x 50mm
Stage locking lever
Slow-close hydraulic slide finger

FOCUS

Coarse adjustment: range of 30mm
Fine adjustment: graduation of 2µm
Tension control knob

ILLUMINATION

Moveable Abbe condenser, NA 1.25,
rack & pinion
Iris diaphragm
100-240V AC / 50-60Hz Auto-Switching Input
Light Options:
Variable LED light source (3W bulb)

Revelation III

| Model # | Description |
|---------------|---|
| R3M-BN4A-DAL3 | Binoc, 4-10-40-100 DIN Achromatic objectives, LED, 100-240vAC w/ 3-prong wall cord |
| R3M-TN4A-DAL3 | Trinoc, 4-10-40-100 DIN Achromatic objectives, LED, 100-240vAC w/ 3-prong wall cord |
| R3M-BN4A-DPL3 | Binoc, 4-10-40-100 DIN Achromatic objectives, LED, 100-240vAC w/ 3-prong wall cord |
| R3M-TN4A-DPL3 | Trinoc, 4-10-40-100 DIN Achromatic objectives, LED, 100-240vAC w/ 3-prong wall cord |
| R3M-MN4A-DAL3 | Monoc, 4-10-40-100 DIN Achromatic objectives, LED, 100-240vAC w/ 3-prong wall cord |

- Medical-Grade Microscope
- Anti-Fungal Coating on All Lenses
- Field-Ready Portable Options (page 2)

WEIGHT AND DIMS

Height: 15" (380mm)
Length: 9" (230mm)
Width: 7" (178mm)
Weight: 14 lbs. (6.4kg)



P 770.270.1394
F 770.270.2389

865 Marathon Parkway
Lawrenceville GA 30046

LWScientific.com

Portable, Rechargeable Revelation III

NEW
ARRIVAL



Includes Rechargeable Battery



Powered by USB Power Adapter



Powered by Laptop USB Port



Powered by Rechargeable Battery

| Model # | Description |
|---------------|---|
| R3M-BN4A-DALP | Portable, Rechargeable Revelation III, Binoc, achromatic objectives, LED illumination, 5V DC Base, USB Cord, & Battery |
| R3M-TN4A-DALP | Portable, Rechargeable Revelation III, Trinoc, achromatic objectives, LED illumination, 5V DC Base, USB Cord, & Battery |