



## ATLANTIS BOTTLE COOLER.

### Model Code:

- Cook N' Cold - **BPD1SK**
- Hot N' Cold - 1 piece hot tank - **BPO1SHS**
- Hot N' Cold - 2 piece hot tank - **BPD1SHS**

### Features:

- Available in Hot N' Cold and Cook N' Cold
- Heavy-duty polyethylene cabinet in white or black
- Stainless steel reservoir
- Available with 1 or 2 piece hot tank
- Large, durable drip tray
- Handle on back for easy transport and placement
- WaterGuard® 7 system eliminates spills during bottle changes and reduces the chance for dust and dirt to enter the cooler reservoir
- Certified to NSF/ANSI 372 for low lead content
- Energy Star certified
- UL Listed
- 3 year limited warranty



**Cabinet:**

Polythelene cabinet with predrilled holes for simple cup dispenser installation.

**Cold Water Refrigeration Unit:**

Convection cooled condenser. Internal, spring mounted, hermetically sealed compressor with automatic overload protector requires no lubrication. Refrigerant is controlled by a capillary tube.

**Cold Water Thermostat:**

Temperature is controlled by an adjustable thermostat and is easily accessible on the rear of the unit.

**Cold Water Reservoir:**

Durable heavy duty type 300 series stainless steel with external copper refrigerant coil encased in pre-fitted molded plastic foam insulation.

**One-Piece Hot Water Tank (BPO model) with fixed thermostat:**

450 watt heating element. One-piece type 300 series stainless steel hot tank is easy to replace or service without breaking soldered refrigeration connections. Fixed thermostat with safety limiter.

**Two-Piece Hot Water Tank (BPD model) with fixed thermostat:**

450 watt heating element is easy to service. Hot tank is a type 300 series stainless steel and can be easily opened for cleaning and removal of mineral deposits. Individual components can be replaced when needed, minimizing the need to replace the entire hot tank. Fixed thermostat with safety limiter.

**Hot Water Capacity:**

45 x 6 oz. cups of piping hot water per hour. 1 1/2 quart storage tank.

**Hot Water Safety Faucet:**

Self-closing activation requires a two-step action that is easy for adults to use, but protects small children.

**Drip Receptor:**

Durable dishwasher safe drip tray lifts out for easy cleaning.

**Electrical:**

115 volts, 60 hertz. 1/20 hp water cooler compressor. Three wire service cord & polarized plug.

**Certifications:**

Product certified to meet lead-free requirements as defined by California, Vermont, and Maryland state laws and the U.S. Safe Drinking Water Act. Model listed by Underwriters laboratories to U.S. and Canadian Standards. Energy Star Certified.

**Warranty:**

Limited 3-year warranty (within the Continental Limits of the U.S. and Canada). Three years on the sealed refrigeration system, one year on most component parts. Detailed warranty certificate enclosed with each cooler; sample copy available upon request.

Specifications are subject to change without notice



**WARNING:**  
Cancer and Reproductive Harm  
[www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

**DIMENSIONS**

		DEPTH	WIDTH	HEIGHT	WEIGHT
<b>BPD1SHS</b>	PRODUCT	13.0"	12.8"	39.8"	28.0 lbs
	PACKAGING	14.4"	14.0"	43.7"	30.7 lbs
<b>BPD1SK</b>	PRODUCT	13.0"	12.8"	39.8"	26.0 lbs
	PACKAGING	14.4"	14.0"	43.7"	29.1 lbs
<b>BPO1SHS</b>	PRODUCT	13.0"	12.8"	39.8"	26.5 lbs
	PACKAGING	14.4"	14.0"	43.7"	29.4 lbs

**COLD WATER CAPACITY**

ROOM TEMP	WATER TEMP	GALLONS PER HOUR AT 50°F	NUMBER OF 3 OZ. CUPS PER HOUR
70°F	70°F	1.4	59
80°F	80°F	1.0	42
90°F	90°F	0.6	25
100°F	100°F	0.4	17

OASIS INTERNATIONAL

222 East Campus View Blvd.  
Columbus, OH 43235

[www.oasiscoolers.com](http://www.oasiscoolers.com)

**1-800-646-2747**