

PORTABLE EMERGENCY EYEWASHES

Self-contained emergency eyewash units, also known as portable eyewash units, contain a large volume reservoir of flushing fluid within to provide a continuous 15-minute flow. They are ideal for locations without access to potable water or for locations where eyewash access needs to be moved at a moments notice. *Haws* portable eyewash units meet all ANSI requirements for flow rates, stream heights, and pressure for the full flushing duration and are CSA certified to ANSI/ISEA Z358.1-2014.



Gravity-Fed Eyewashes



7500 GRAVITY-FED, PORTABLE EYEWASH

FDA approved high-density green polyethylene 16-gallon (60.6 L) tank supplies a continuous flow of clean water for a full 15 minutes at .4 GPM (1.5 LPM). Easily activated by pulling the yellow activation arm down to the open position.

Global: B549155



7501 GRAVITY-FED, COMPACT PORTABLE EYEWASH

Portable 9-gallon (34.1 L) eyewash, polyethylene tank with yellow pull-down activation arm. The unit supplies a continuous flow of water for a full 15 minutes at .4 GPM (1.5 LPM).

Global: B549153

Tempered Gravity-Fed Eyewashes



Tempered

7501T GRAVITY-FED, TEMPERED PORTABLE EYEWASH

Portable 9-gallon (34.1 L) tempered portable eyewash with a heated, insulated blanket to provide ANSI compliant tempered, potable water in ambient operating temperatures from -20°F (-29°C) to 100°F (38°C). 120V electrical requirement with supplied 8' GFCI power cord. Additional HazLoc and 240V options available.

Global: B2246768



Tempered

7501BL 120V INSULATED BLANKET

Heated, insulated blanket to provide ANSI compliant tempered, potable water in ambient operating temperatures from -20°F (-29°C) to 100°F (38°C). The self-contained heating blanket easily installs on to existing model 7501 units and the electrical system uses NEMA 3R rated components. 120V electrical requirement with supplied 8' GFCI power cord. Eyewash and heating blanket offered as a package or individually. Additional HazLoc and 240V options available.

Global: B2246767

Air-Pressurized Eyewashes



7603 AIR PRESSURIZED, PORTABLE EYEWASH

Portable 15-gallon (57 L) eyewash with stainless steel tank with an air pressure gauge, pressure relief valve, tire-type air fill valve. The unit provides approximately 10 usable gallons (37.9 liters) of water for effective rinsing. Optional transport cart, Model 9008, and optional drench hose, Model 8901B, available.

Global: B2246769

Eyewash Cleansing Sticks



9083 HAWSCLEAN™ PORTABLE EYEWASH CLEANSING STICK

HawsCLEAN™ cleansing stick is the safe and effective way to prevent the growth of Legionella, E-Coli and other harmful bacteria in most portable gravity fed or pressurized emergency eyewash equipment.

Global: 290413