

AQUARIUS BOTTOM LOAD BOTTLE COOLER.

Model Code:

Tri-temp - BAEB1SHSK

Features:

- Bottom load, no lifting heavy bottles
- Hot, Cold and Room Temp from a single dispense point
- Polymer cabinet won't rust or scratch the floor
- Indicator lights for power, heating, cooling and empty bottle
- Stainless steel reservoir
- Handle on back for easy transport and placement
- Extra high 11" dispense height makes it easy to fill large sports bottles
- Commercial cooling capacity; compressordriven refrigeration system
- Removable drip tray
- · Lighted alcove illuminates dispensing area
- Certified to NSF/ANSI 372 for low lead content
- Energy Star certified
- UL Listed
- 3 year limited warranty









Cabinet:

High impact polymer cabinet

Cold Water Refrigeration Unit:

Convection cooled condenser. Internal, spring mounted, hermetically sealed compressor with automatic overload protector requires no lubrication. Refrigerant is controlled by a capillary tube.

Cold Water Thermostat:

Temperature is controlled by a pre-set thermostat for maximum performance.

Cold Water Reservoir:

Type 300 series stainless steel with external refrigerant coil. Molded reservoir insulation is expanded bead polystyrene.

One-Piece Hot Water Tank:

420 watt heating element for fast, and efficient heating. Hot tank is a type 300 series stainless steel.

Hot Water Capacity:

30 x 6 oz. cups of piping hot water per hour. 1 quart storage tank.

Hot Water Thermostat:

Fixed thermostat with safety limiter.

Hot Water Safety Faucet:

Self-closing activation requires a two-step action that is easy for adults to use but protects small children.

Drip Receptor:

Durable 2-piece drip tray lifts out for easy cleaning.

Electrical:

115 volts, 60 hertz. 1/12 hp water cooler compressor. Three wire service cord & polarized plug.

Certifications:

Product certified to meet lead-free requirements as defined by California, Vermont, and Maryland state laws and the U.S. Safe Drinking Water Act. Model listed by Underwriters laboratories to U.S. and Canadian Standards. Energy Star Certified.

Warranty:

Limited 3-year warranty (within the Continental Limits of the U.S. and Canada). Three years on the sealed refrigeration system, one year on most component parts. Detailed warranty certificate enclosed with each cooler; sample copy available upon request.

Specifications are subject to change without notice



WARNING:

Cancer and Reproductive Harm www.P65Warnings.ca.gov

DIMENSIONS

		DEPTH	WIDTH	HEIGHT	WEIGHT
BAEB1SHSK	PRODUCT	14.0"	12.9"	43.5"	33.7 lbs
	PACKAGING	14.8"	13.8"	46.9"	38.4 lbs

COLD WATER CAPACITY

ROOM TEMP	WATER TEMP	GALLONS PER HOUR AT 50°F	NUMBER OF 3 OZ. CUPS PER HOUR
70°F	70°F	1.4	59
80°F	80°F	1.0	42
90°F	90°F	0.6	25
100°F	100°F	0.4	17



OASIS INTERNATIONAL

222 East Campus View Blvd. Columbus, OH 43235

www.oasiscoolers.com

1-800-646-2747