



STAINLESS STEEL  
**WORK TABLES**

**SUPER SAVER Series - 5" Backsplash - Open Base Style**



Item #: \_\_\_\_\_ Qty #: \_\_\_\_\_  
 Model #: \_\_\_\_\_  
 Project #: \_\_\_\_\_



**Rolled Rim Edges  
on Front & Splash  
on Back and Square  
Side Edges**



**1-5/8" LEG STRETCHERS  
Ensure Stability**

**FEATURES:**

Top is furnished with 1 5/8" sanitary rolled rim edge on front and square sides, and a 5" splash with a 1" return on the rear side.

TWO hat channels stud welded to reinforce and maintain a level working surface. 30" and 36" wide tables supplied with THREE hat channels.

Pre-engineered welded angle adapters insure ease of future drawer installation.

Front to back Stretchers are welded to legs. Left to right Stretcher bolted to legs and requires assembly.

**CONSTRUCTION:**

All TIG welded. Exposed weld areas polished to match adjacent surfaces.

Entire top mechanically polished to a satin finish.

Top is sound deadened.

Roll formed embossed galvanized hat channels are secured to top by means of structural adhesive and weld studs.

Gussets welded to support hat sections.

**MATERIAL:**

**TSKG-SERIES: Stainless Steel Legs - Open Base**

**TOP:** 16 gauge stainless steel type "430" series.

**STRETCHERS:** 1 5/8" dia. tubular stainless steel.

**LEGS:** 1 5/8" diameter tubular stainless steel.  
1" adjustable stainless steel bullet feet.  
Stainless steel gussets.

**TKAG-SERIES: Galvanized Legs - Open Base**

**TOP:** 16 gauge stainless steel type "430" series.

**STRETCHERS:** 1 5/8" dia. tubular galvanized steel.

**LEGS:** 1 5/8" diameter tubular galvanized steel.  
1" adjustable plastic bullet feet.

Galvanized steel gussets.

**TSKG-Series:  
Stainless Steel Legs & Stretchers**

L	24" Wide	30" Wide	36" Wide
30"	TSKG-240	TSKG-300	
24"	TSKG-242	TSKG-302	
36"	TSKG-243	TSKG-303	TSKG-363
48"	TSKG-244	TSKG-304	TSKG-364
60"	TSKG-245	TSKG-305	TSKG-365
72"	TSKG-246	TSKG-306	TSKG-366
84"	TSKG-247	TSKG-307	TSKG-367
*96"	TSKG-248	TSKG-308	TSKG-368
*108"	TSKG-249	TSKG-309	TSKG-369
*120"	TSKG-2410	TSKG-3010	TSKG-3610
*132"	TSKG-2411	TSKG-3011	TSKG-3611
*144"	TSKG-2412	TSKG-3012	TSKG-3612



**TKAG-Series:  
Galvanized Steel Legs & Stretchers**

L	24" Wide	30" Wide	36" Wide
30"	TKAG-240	TKAG-300	
24"	TKAG-242	TKAG-302	
36"	TKAG-243	TKAG-303	TKAG-363
48"	TKAG-244	TKAG-304	TKAG-364
60"	TKAG-245	TKAG-305	TKAG-365
72"	TKAG-246	TKAG-306	TKAG-366
84"	TKAG-247	TKAG-307	TKAG-367
*96"	TKAG-248	TKAG-308	TKAG-368
*108"	TKAG-249	TKAG-309	TKAG-369
*120"	TKAG-2410	TKAG-3010	TKAG-3610
*132"	TKAG-2411	TKAG-3011	TKAG-3611
*144"	TKAG-2412	TKAG-3012	TKAG-3612

\*Units 8 ft. and larger are furnished with six (6) legs

**Create Your Own Efficient Workstation with the Available Standard Accessories (Visit Section K)**



**Customer Service Available To Assist You 1-800-645-3166 8:30 am - 7:00 pm E.S.T.**

For Orders & Customer Service:

Email: customer@advancetabco.com or Fax: 631-242-6900

For Smart Fabrication™ Quotes:


Email: smartfab@advancetabco.com or Fax: 631-586-2933

# DETAILS and SPECIFICATIONS



ALL DIMENSIONS ARE TYPICAL TOL ± .500"

All Units Shipped Unassembled (KD) for Reduced Shipping Costs.

## TSKG & TKAG Series Open Base Style 5" Backsplash



Units 8 ft. and larger are furnished with six (6) legs



### TSKG-Series: Stainless Steel Legs & Stretchers

L	24" Wide	Wt.	30" Wide	Wt.	36" Wide	Wt.
30"	TSKG-240	49 lbs.	TSKG-300	55 lbs.		
24"	TSKG-242	43 lbs.	TSKG-302	48 lbs.		
36"	TSKG-243	55 lbs.	TSKG-303	62 lbs.	TSKG-363	80 lbs.
48"	TSKG-244	67 lbs.	TSKG-304	75 lbs.	TSKG-364	85 lbs.
60"	TSKG-245	77 lbs.	TSKG-305	89 lbs.	TSKG-365	99 lbs.
72"	TSKG-246	89 lbs.	TSKG-306	97 lbs.	TSKG-366	112 lbs.
84"	TSKG-247	107 lbs.	TSKG-307	118 lbs.	TSKG-367	131 lbs.
96"	TSKG-248	119 lbs.	TSKG-308	131 lbs.	TSKG-368	145 lbs.
108"	TSKG-249	135 lbs.	TSKG-309	150 lbs.	TSKG-369	165 lbs.
120"	TSKG-2410	234 lbs.	TSKG-3010	249 lbs.	TSKG-3610	268 lbs.
132"	TSKG-2411	258 lbs.	TSKG-3011	276 lbs.	TSKG-3611	298 lbs.
144"	TSKG-2412	273 lbs.	TSKG-3012	291 lbs.	TSKG-3612	313 lbs.

### TKAG-Series: Galvanized Steel Legs & Stretchers

L	24" Wide	Wt.	30" Wide	Wt.	36" Wide	Wt.
30"	TKAG-240	49 lbs.	TKAG-300	55 lbs.		
24"	TKAG-242	43 lbs.	TKAG-302	48 lbs.		
36"	TKAG-243	55 lbs.	TKAG-303	62 lbs.	TKAG-363	80 lbs.
48"	TKAG-244	67 lbs.	TKAG-304	75 lbs.	TKAG-364	85 lbs.
60"	TKAG-245	77 lbs.	TKAG-305	89 lbs.	TKAG-365	99 lbs.
72"	TKAG-246	89 lbs.	TKAG-306	97 lbs.	TKAG-366	112 lbs.
84"	TKAG-247	107 lbs.	TKAG-307	118 lbs.	TKAG-367	131 lbs.
96"	TKAG-248	119 lbs.	TKAG-308	131 lbs.	TKAG-368	145 lbs.
108"	TKAG-249	135 lbs.	TKAG-309	150 lbs.	TKAG-369	165 lbs.
120"	TKAG-2410	234 lbs.	TKAG-3010	249 lbs.	TKAG-3610	268 lbs.
132"	TKAG-2411	258 lbs.	TKAG-3011	276 lbs.	TKAG-3611	298 lbs.
144"	TKAG-2412	273 lbs.	TKAG-3012	291 lbs.	TKAG-3612	313 lbs.



ADVANCE TABCO is constantly engaged in a program of improving our products. Therefore, we reserve the right to change specifications without prior notice.