BULK BAG LIFTER - BBL-4

APPROX WEIGHT: 90.86 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE

53 1/2" 41 3/4" 47 3/4" 35 3/4" 167/8" 35 3/4" 17 7/8" APPROX. WEIGHT / LOST LOAD = 97 LBS. CAPACITY = 4,000 # EVENLY DISTRIBUTED NEVER EXCEED LOAD CENTER RATING PER FORK 39 15/16 TRUCK MANUFACTURER'S GUIDELINES EFFECTIVE THICKNESS WILL VARY DEPENDING **ON APPLICATION & TYPE OF FORK TRUCK** 2" CENTER OF GRAVITY 10 7/16" 1 1/2" 67/8 FOR INTERNAL USE ONLY 3 1/4" 5/8' **PROJECT SIGN OFF** SALES DIMENSION TOLERANCE ± 1/4" ENG. ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS FAB. ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON POWER STANDARD FEATURES I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION MODEL NUMBER IS BBL-4 REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO Α CAPACITY IS 4,000 LBS CONFIRM PRODUCT AND INSTALLATION Ρ OVERALL WIDTH IS 53 1/2" COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE Ρ USABLE WIDTH IS UP TO 35 3/4" AND LOCAL REGULATIONS AND STANDARDS. R DEPENDING ON BAG STRAPS ANY MODIFIED UNITS ARE NON-RETURNABLE 0 OVERALL LENGTH IS 39 15/16" [] As drawn [] As marked V USABLE LENGTH IS 35 3/4" Α Signed: Date: OVERALL HEIGHT IS 10 7/16" L **BAG LINER HOOK** Printed Name: FORK TRUCK RESTRAINT STRAP 48 1/2" LG LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING P.O.# X DISTRIBUTOR'S NAME: VESTIL MANUFACTURING W.O.# Х DRAWN BY: SALES: X DATE: RAI SPECIAL FEATURES 06/17/2014 REFERENCE: X SCALE: 1:18 FILE NAME: NONE QUOTED LEAD TIME: X 47-007-011 QUOTE # х