

**800  
SERIES**

**INDUSTRIAL KD CABINETS**

**2 YEAR  
WARRANTY**

**Features:**

- All components precision engineered with no bolt heads showing on front and side panels.
- 20 gauge body and 22 gauge shelves provide strength and durability.
- Shelves easily adjust up or down in 2" increments. Triple flanged shelf front for added strength (capacity up to 250 lbs).
- Reinforced doors swing a full 180°.
- Doors are factory-hung in 16 gauge frames ensuring proper performance.
- 16 gauge continuous hinges.
- Corner foot gussets provide added rigidity and stability (replaced by mounting plates on mobile units).
- Mobile units include four heavy-duty locking swivel casters.
- Positive three-point locking (top, center and bottom) for secure locking.
- Plated locking handle has built-in cylinder key lock (keys included).

**Configurations:**

- Storage (includes 4 adjustable shelves)
- Wardrobe (includes 1 shelf and coat rod)
- Combination (includes 1 full width shelf, 3 half width shelves and a half width coat rod)

**Door Options:**

- Solid
- Safety-View (includes polycarbonate panels in door)
- Ventilated (includes expanded metal panels in door)



STATIONARY WARDROBE  
SOLID DOORS



MOBILE STORAGE  
SOLID DOORS



STATIONARY STORAGE  
VENTILATED DOORS



STATIONARY COMBINATION  
SAFETY-VIEW DOORS

Provides maximum protection to tools, dies, delicate instruments, supplies, and personal belongings. Neat and attractive in appearance. Designed to meet government requirements.

Description	Width	Depth	Height	Knock-Down Cat No.	Assembled Cat No.	Color Selection	+Medsafe Antimicrobial
<b>SOLID DOOR CABINETS, 800 SERIES</b>							
Stationary, Storage	36	18	78	815S18	815S18A	ME, PT	PL-AM
Stationary, Storage	36	24	78	815S24	815S24A	ME, PT	PL-AM
Stationary, Storage	48	18	78	825S18	825S18A	ME, PT	PL-AM
Stationary, Storage	48	24	78	825S24	825S24A	ME, PT	PL-AM
Stationary, Wardrobe	36	18	78	835W18	835W18A	ME, PT	PL-AM
Stationary, Wardrobe	36	24	78	835W24	835W24A	ME, PT	PL-AM
Stationary, Wardrobe	48	18	78	845W18	845W18A	ME, PT	PL-AM
Stationary, Wardrobe	48	24	78	845W24	845W24A	ME, PT	PL-AM
Stationary, Combination	36	18	78	855C18	855C18A	ME, PT	PL-AM
Stationary, Combination	36	24	78	855C24	855C24A	ME, PT	PL-AM
Stationary, Combination	48	18	78	865C18	865C18A	ME, PT	PL-AM
Stationary, Combination	48	24	78	865C24	865C24A	ME, PT	PL-AM
Mobile, Storage	36	24	78	815S24M	815S24MA	ME, PT	PL-AM
Mobile, Storage	48	24	78	825S24M	825S24MA	ME, PT	PL-AM
<b>SAFETY VIEW DOOR CABINETS, 800 SERIES</b>							
Stationary, Storage	36	18	78	815S18SV	815S18SVA	ME, PT	PL-AM
Stationary, Storage	36	24	78	815S24SV	815S24SVA	ME, PT	PL-AM
Stationary, Storage	48	18	78	825S18SV	825S18SVA	ME, PT	PL-AM
Stationary, Storage	48	24	78	825S24SV	825S24SVA	ME, PT	PL-AM
Stationary, Wardrobe	36	18	78	835W18SV	835W18SVA	ME, PT	PL-AM
Stationary, Wardrobe	36	24	78	835W24SV	835W24SVA	ME, PT	PL-AM
Stationary, Wardrobe	48	18	78	845W18SV	845W18SVA	ME, PT	PL-AM
Stationary, Wardrobe	48	24	78	845W24SV	845W24SVA	ME, PT	PL-AM
Stationary, Combination	36	18	78	855C18SV	855C18SVA	ME, PT	PL-AM
Stationary, Combination	36	24	78	855C24SV	855C24SVA	ME, PT	PL-AM
Stationary, Combination	48	18	78	865C18SV	865C18SVA	ME, PT	PL-AM
Stationary, Combination	48	24	78	865C24SV	865C24SVA	ME, PT	PL-AM
Mobile, Storage	36	24	78	815S24SVM	815S24SVMMA	ME, PT	PL-AM
Mobile, Storage	48	24	78	825S24SVM	825S24SVMMA	ME, PT	PL-AM
<b>VENTILATED DOOR CABINETS, 800 SERIES</b>							
Stationary, Storage	36	18	78	815S18EV	815S18EVA	ME, PT	PL-AM
Stationary, Storage	36	24	78	815S24EV	815S24EVA	ME, PT	PL-AM
Stationary, Storage	48	18	78	825S18EV	825S18EVA	ME, PT	PL-AM
Stationary, Storage	48	24	78	825S24EV	825S24EVA	ME, PT	PL-AM
Stationary, Wardrobe	36	18	78	835W18EV	835W18EVA	ME, PT	PL-AM
Stationary, Wardrobe	36	24	78	835W24EV	835W24EVA	ME, PT	PL-AM
Stationary, Wardrobe	48	18	78	845W18EV	845W18EVA	ME, PT	PL-AM
Stationary, Wardrobe	48	24	78	845W24EV	845W24EVA	ME, PT	PL-AM
Stationary, Combination	36	18	78	855C18EV	855C18EVA	ME, PT	PL-AM
Stationary, Combination	36	24	78	855C24EV	855C24EVA	ME, PT	PL-AM
Stationary, Combination	48	18	78	865C18EV	865C18EVA	ME, PT	PL-AM
Stationary, Combination	48	24	78	865C24EV	865C24EVA	ME, PT	PL-AM
Mobile, Storage	36	24	78	815S24EVM	815S24EVMMA	ME, PT	PL-AM
Mobile, Storage	48	24	78	825S24EVM	825S24EVMMA	ME, PT	PL-AM



708  
BLACK  
(ME)

729  
TAN  
(PT)

711  
ANTIMICROBIAL  
LIGHT GRAY  
(PL-AM)



Order your cabinets in our specially formulated Antimicrobial powder coat finish that protects against bacteria, mold & yeast for up to 20 years!