

RIDGID®

RP 350 & RP 351 Standard Press Tool Unmatched performance. Zero timeouts.



The new RIDGID® RP 350 and RP 351 feature a brushless motor that is capable of over 100,000 press cycles and requires no scheduled maintenance. Get access to hard-to-reach locations with endless 360° swivel. With the most advanced LED lighting and color-coded status indicators, the RP 350 and RP 351 have been upgraded from top to bottom. They are the only press tools in the industry that are compatible with all RIDGID Standard Series press jaws, rings, actuators and attachments.

- Durable: Brushless motor capable of over 100,000 press cycles
- Relentless: No scheduled maintenance
- Agile: Endless 360° head swivel for reaching tight spaces
- Smart: Bluetooth connectivity and color-coded light indicators for easy operation
- Bright: Robust LED lighting for low-light applications

THE ALL-DAY PERFORMANCE PRESS TOOL.

SPECIFICATIONS

- Capacity 1/2" to 4" Copper, 1/2" to 4" Carbon Steel*, and 1/2" to 2" PEX
- Power 18V Advanced Lithium Ion Battery
- Hydraulic Ram Output..... 7,200 lbs. (32 kN)
- Weight (Tool Only) RP 350: 7.1 lbs. (3.2 kg) RP 351: 7.1 lbs. (3.2 kg)
- Dimensions

	RP 350	RP 351
Length	11.3" (287 mm)	15.6" (396 mm)
Height.....	11.0" (280 mm)	4.6" (117 mm)
Width.....	3.1" (79 mm)	3.0" (76 mm)
- Barrel/Jaw Swivel Angle 360°
- Crimp Cycle Time..... 4.5 seconds
- Presses Per Charge >325**
- Lighting..... LED light for no- or low-light environments
- Service Cycle Interval..... No scheduled maintenance

* Press Booster is needed for 2 1/2" to 4"

** Based on pressing 3/4" fittings on Type L copper. Dependent upon pipe material, size, type of fitting and other factors.



ORDER INFORMATION

CATALOG NO.	DESCRIPTION	WEIGHTS (lb.) (kg)		PACK. QTY.
RP 350				
67053	RP 350 Battery Kit w/ProPress Jaws (1/2" - 2")	50.8	23.0	1
67058	RP 350 Battery Kit w/ProPress Jaws (1/2" - 1")	30.8	14.0	1
67063	RP 350 Battery Kit (No Jaws)	18.8	8.5	1
67068	RP 350 Corded Kit w/ProPress Jaws (1/2" - 2")	47.8	21.7	1
67073	RP 350 Corded Kit w/ProPress Jaws (1/2" - 1")	27.8	12.6	1
67078	RP 350 Corded Kit (No Jaws)	15.8	7.1	1
67083	RP 350 Press Tool Only	7.1	3.2	1
RP 351				
67178	RP 351 Battery Kit w/ProPress Jaws (1/2" - 2")	50.7	23.0	1
67183	RP 351 Battery Kit w/ProPress Jaws (1/2" - 1")	30.7	13.9	1
67188	RP 351 Battery Kit (No Jaws)	18.7	8.5	1
67193	RP 351 Corded Kit w/ProPress Jaws (1/2" - 2")	47.7	21.7	1
67198	RP 351 Corded Kit w/ProPress Jaws (1/2" - 1")	27.7	12.6	1
67218	RP 351 Corded Kit (No Jaws)	15.7	7.1	1
67223	RP 351 Press Tool Only	7.0	3.2	1
Accessories				
67338	Carrying Case	7.9	3.6	1
56513	Battery, 18V 2.5 Ah Lithium Ion	1.1	0.5	1
56518	Battery, 18V 5.0 Ah Lithium Ion	1.6	0.7	1
64383	Charger, 120V	1.6	0.7	1
44798	Charger Replacement Cord	0.3	0.1	1
64203	Charger Replacement Car Cord	0.3	0.1	1

All kits include RP 350 or RP 351, two 12V batteries, charger and carrying case.



360° SWIVEL HEAD



RP 350 Kit (67053)



RP 351 Kit (67178)



999-997-3411.10

Viega® is a registered trademark of Viega GmbH & Co. PureFlow® is a registered trademark of Viega LLC.

All sales subject to Ridge Tool Company Terms and Conditions of Sales. Catalog Sheet No. R-20-I (221) Effective Date: October 1, 2020

©2020, 2021 Ridge Tool Company. All rights reserved. RIDGID and the Emerson logo are registered trademarks of Emerson Electric Co. or its subsidiaries in the US and other countries. All other trademarks belong to their respective holders.