



**Product Family**  
**Uvex Stealth**








Futuristic, low profile design for chemical splash and impact. Toric lens provides superior optics and peripheral vision. Quick adjust headband.

**Learn more about all of our Uvex plano products at [uvex.us](http://uvex.us) >**

**Learn more about our Uvex Rx safety frames at [uvexrx.com](http://uvexrx.com) >**



**Product Numbers & Ordering Information**

Product Numbers	Details
 S3960C-BR	<b>Gray Body, Neoprene Band</b> Clear Lens,Uvextreme Anti-fog Coating, CA 19,072
 S3960CI-BR	<b>Gray Body, Fabric Band</b> Clear Lens,Uvextreme Anti-fog Coating, CA 19,072
 S3960D-BR	<b>Gray Body, Neoprene Band</b> Clear Lens, Dura-streme Dual (Anti-fog / Anti-scratch) Coating, CA 19,072
 S3961C-BR	<b>Gray Body, Neoprene Band</b> Gray Lens,Uvextreme Anti-fog Coating, CA 19,072
 S3962C-BR	<b>Gray Body, Neoprene Band</b> Amber Lens,Uvextreme Anti-fog Coating, CA 19,072
 S3959	<b>Rx Carrier</b>
 S3959-BR	<b>Rx Carrier</b>

Uvex Stealth



S3960C

**Gray Body, Neoprene Band**  
Clear Lens, Uvextreme Anti-fog Coating

---



S3960CI

**Gray Body, Fabric Band**  
Clear Lens, Uvextreme Anti-fog Coating

---



S3960D

**Gray Body, Neoprene Band**  
Clear Lens, Dura-streme Dual (Anti-fog / Anti-scratch) Coating

---



S3961C

**Gray Body, Neoprene Band**  
Gray Lens, Uvextreme Anti-fog Coating

---



S3962C

**Gray Body, Neoprene Band**  
Amber Lens, Uvextreme Anti-fog Coating

---



S39610C

**Teal Body, Neoprene Band**  
Clear Lens, Uvextreme Anti-fog Coating

---



S39611C

**Teal Body, Neoprene Band**  
Gray Lens, Uvextreme Anti-fog Coating

---



S39630C

**Orange Body, Neoprene Band**  
Clear Lens, Uvextreme Anti-fog Coating

---



S39630CI

**Orange Body, Fabric Band**  
Clear Lens, Uvextreme Anti-fog Coating

---



S39631C

**Orange Body, Neoprene Band**  
Gray Lens, Uvextreme Anti-fog Coating

---



S821

**Replacement Neoprene Headband w/out slides**

---



S823

**Replacement Flame Resistant Fabric Headband**

---



S700C

**Replacement Lens**  
Clear Lens, Uvextreme Anti-fog Coating

---

## Uvex Stealth



S700C-BR

### Replacement Lens

Clear Lens, Uvextreme Anti-fog Coating



S701C

### Replacement Lens

Gray Lens, Uvextreme Anti-fog Coating



S701C-BR

### Replacement Lens

Gray Lens, Uvextreme Anti-fog Coating



S702C

### Replacement Lens

Amber Lens, Uvextreme Anti-fog Coating



S702C-BR

### Replacement Lens

Amber Lens, Uvextreme Anti-fog Coating



S700D

### Replacement Lens

Clear Lens, Dura-streme Dual (Anti-fog / Anti-scratch) Coating



S8999

### Rx Pattern

### Packaging Information

Packaging Ind. Box, 50/case

## Overview

### Key Features

Never before have goggles offered such comfort and protection as well as sleek, futuristic styling. The Uvex Stealth goggle combines modern design, technology, materials and high-performance lens coatings to create the highest levels of worker comfort and acceptance. One of the most popular goggles on the market, the Uvex Stealth makes it easy — even fashionable — to wear goggles on the job.

- Futuristic, low profile design for chemical splash and impact
- Toric lens provides superior optics and peripheral vision
- Rx insert available
- Easiest lens replacement system available
- Uvextreme AF coating and indirect ventilation system minimize fogging
- Dura-streme technology option delivers Uvextreme anti-fog protection on the interior of the lens and Ultra-dura hardcoat on the exterior of the lens for greater chemical and scratch resistance and longer lens life
- Quick-adjust headband
- Made in USA

### Recommended Industries/Use

- Chemical
- Construction
- Law Enforcement
- Manufacturing
- Mining
- Municipal Services
- Oil and Gas
- Pharmaceutical
- Steel and Metals
- Transportation
- Utilities

### Hazards

- Abrasion
- Airborne Particulates
- Biohazard
- Chemical
- Impact
- Low Visibility
- Splash

### Regulations

- ANSI Z87+ - Meets ANSI Z87+ (High Impact) standard
- ANSI.Z.87.1/1989, CA 19,072 - Meets ANSI.Z.87.1/1989, CA 19,072
- CSA Z94.3 - Tested by Honeywell to meet the requirements of the CSA Z94.3 standard

#### Historical Brand

Uvex

#### Warranty Information

Limited warranty

## Specifications

#### Lens overall width

- 165 mm (6.25) "

#### Lens material

- Polycarbonate

#### Lens coating

- Uvextreme® AF

#### Lens thickness

- 1.6 mm (0.06) "

#### Available lens tints

- Clear, Gray, Amber

#### Replacement lenses available (yes/no)

- Yes

#### Rx capable

- Specially designed Rx carrier available (S3959)

#### Goggle body material

- Polypropylene with elastomer

#### Headband material

- Neoprene, fabric

#### Goggle weight

- 75.20 grams (2.7oz)

#### Available body colors

- Gray/Gray, Teal/Gray

#### Country of origin

- Made in U.S.A

## Certifications

#### ANSI Certificate of Compliance\_Eng

[http://www.honeywellsafety.com/Supplementary/Documents\\_and\\_Downloads/Eye\\_and\\_Face\\_Protection/Laser\\_Filters\\_\\_\\_Eyewear/19294/1033.aspx](http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Eye_and_Face_Protection/Laser_Filters___Eyewear/19294/1033.aspx)

ANSI Certificate of Compliance\_Eng

#### ANSI Certificate of Compliance\_Spanish

[http://www.honeywellsafety.com/Supplementary/Documents\\_and\\_Downloads/Eye\\_and\\_Face\\_Protection/Laser\\_Filters\\_\\_\\_Eyewear/19295/1033.aspx](http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Eye_and_Face_Protection/Laser_Filters___Eyewear/19295/1033.aspx)

ANSI Certificate of Compliance\_Spanish

## Literature & Documents

## Uvex Stealth

### Data Sheet Uvex Stealth Goggle-Eng

[http://www.honeywellsafety.com/Supplementary/Documents\\_and\\_Downloads/Eye\\_and\\_Face\\_Protection/Goggles/19066/1033.aspx](http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Eye_and_Face_Protection/Goggles/19066/1033.aspx)

Data Sheet Goggle Uvex Stealth-Eng

### Uvex Stealth\_DS\_ESP

[http://www.honeywellsafety.com/Supplementary/Documents\\_and\\_Downloads/Eye\\_and\\_Face\\_Protection/Goggles/41036/1033.aspx](http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Eye_and_Face_Protection/Goggles/41036/1033.aspx)

Uvex Stealth Nunca antes han ofrecido tanto confort y proteccion, a la par de un estilo futurista y envolvente. Uvex Stealth un diseo moderno, tecnologa y recubrimientos con materiales de alto desempeo para crear un nivel mayor de confort y aceptacin del trabajador. Uvex Stealth una de las gafas ms pouplares del mercado

## Training & Proper Use

All products come packaged with instructions and warnings for proper use.

## Technical Support

(800) 682-0839, Sperian Protection Americas, Customer Care

### RELATED PRODUCTS

© Honeywell International Inc.