

Engineered
for the **EXTREME**



Uvex Livewire[™]
SEALED EYEWEAR

UVEX[™]
by Honeywell

EXTREME ENVIRONMENTS

Some workplaces demand eye protection that performs at a higher level. Places where debris—from dust, to sand, to dirt and soot—combine with wind, sun, heat and sweat to create a challenging environment. Extreme environments like this demand extreme eye protection.

EXTREME WORKERS

Every day, workers in extreme environments are exposed to hazards that can lead to serious injury. And when it comes to vision protection, these workers have specific needs. From oil and gas operations to mining to heavy construction, performance is critical. Workers in these extreme environments deserve extreme eye protection.

Uvex Livewire™ Sealed Eyewear

ENGINEERED FOR THE EXTREME.

Extreme protection for extreme workers and working conditions.

After visiting these job sites and talking to workers and safety managers, we heard loud and clear that finding the right eye protection can be a challenge. Workers are exposed to wind, sun, dirt, dust and debris, as well as heat and humidity. Keeping debris out of their eyes while keeping lenses clear of fogging—no matter how hot or intense the work gets—is a must. That's why we created Uvex Livewire sealed eyewear.

Designed from the ground up based on in-the-field research, Uvex Livewire sealed eyewear delivers the fit, performance and protection you won't find anywhere else. It's also available in a prescription frame option to outfit even more of your team. With its precision-designed fit, best-in-class anti-fog lens coating and comfort-engineered materials built into the frame, Uvex Livewire sealed eyewear is worthy of the most demanding environments...and worthy of the hardest working individuals.





by Honeywell



PERFORMANCE

10X ANTI-FOG **2X** SCRATCH RESISTANCE

In extreme environments, anti-fog performance and durability are required to keep workers protected. Uvex Livewire sealed eyewear delivers on all counts.

- Lenses feature proprietary Uvextreme Plus® anti-fog coating for superior, long-lasting fog-free vision. Most anti-fog coatings perform well right out of the box, but their effectiveness will diminish over time. Permanently bonded to the lens, Uvextreme Plus promises anti-fog protection that lasts up to 10X longer* — even after extended wear and repeated washings.
- Uvextreme Plus also provides 2X better scratch-resistance* than competitive anti-fog coated products for longer-lasting lenses.
- Top and side channels in the frame are strategically placed and designed for optimal venting to enhance anti-fog performance while keeping out dust and debris.
- Designed to stand up to the harshest conditions, Dura-streme® lenses combine two high-performance lens coatings on one lens — Uvextreme® anti-fog on the interior and Ultra-dura® anti-scratch on the exterior — for up to 3x longer lens life.*
- Offered in the widest assortment of lens tints utilizing Uvex Spectrum Control Technology® (SCT) lenses. Available in Clear, Amber, Espresso, Gray, SCT-Reflect 50 (indoor/outdoor mirror), SCT-Gray, SCT-Low IR, Shade 3.0, Shade 5.0 — from low light, to glare, to infrared protection, there's a Uvex Livewire lens for the job.
- 100% dielectric
- Meets the ANSI Z87.1-2010 standard
- Certified to the requirements of the CSA Z94.3 standard
- *Not for chemical splash applications*

*Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application. Anti-fog performance based on independent lab test results.



Subframe



Temple and ratchet



Side vents



Temple tips

FIT AND COMFORT

In high-particulate environments that require sealed eyewear, a proper fit is absolutely critical. Through extensive research and fit-testing on hundreds of workers, Uvex Livewire sealed eyewear sets the bar for achieving a proper fit on even the hardest to fit individuals.

- Smooth surface and density of foam are designed to minimize pressure against the skin
- Contoured design minimizes bulk for superior comfort and enhanced line of sight
- Precise placement of vents ensures air circulation while minimizing gaps
- The curvature of browbar is optimized based on morphological data to fit a large number of wearers
- Ratcheting temples adjust lens angle by up to 15° for optimal coverage and air circulation
- Flexible design can be worn with temples like a spectacle or with the headband like a goggle depending on the application
- Simple temple-to-headband exchange system makes switching between temples or headband quick and easy
- Streamlined, wraparound frame design accommodates respirators and other PPE, while the low-profile temples fit comfortably with earmuffs
- Padded temples are engineered to provide ideal tension and flex for superior comfort and fit
- Cloth headband is latex free and also features a ratchet for greater adjustability

Uvex SW09 Livewire™ Sealed Rx Eyewear

A very important – and often overlooked – aspect of delivering a comprehensive safety eyewear program is vision correction. With research showing that up to 50% of workers require some degree of vision correction, no safety eyewear program is complete without a prescription option. To meet the needs of workers who require vision correction, we offer the Uvex SW09 Livewire Rx safety frame through Prescription Safety Eyewear Providers*. Built with the same sealed eyewear performance and fit, the Uvex SW09 Livewire prescription safety frame comes in three colors and a 6-base and 8-base lens configuration to accommodate almost any prescription.



Black frame




Red frame



Blue frame

The 8-base version, with its deeper curvature, offers the highest visibility and added peripheral vision; however it can accommodate only a limited prescription range. So we offer a 6-base version to expand the prescription range to cover most employees. Your Prescription Safety Eyewear Provider or optical lab will be able to determine which version frame your employee needs based on their prescription.



This side shown with 8-base Rx lens configuration.

This side shown with 6-base Rx lens configuration.

(Meets the ANSI-Z87.1-2010 and CSA Z94.3 standards. *The Rx version should be purchased through certified safety labs or providers of programs that use certified labs as required by ANSI guidelines.)



To add the Uvex SW09 Livewire RX sealed eyewear frame to your Prescription Safety Eyewear Program, simply **download the Rx sizing card** and pass it on to your current supplier. If you do not have a Prescription Safety Eyewear Program or if you need to locate a Provider, we can help. Please call 1 (800) 446-1802 to speak with one of our Customer Care representatives.

UVEX[™]
by Honeywell

Uvex Livewire™



Clear — Ideal for most indoor work applications



Espresso — minimizes strong outdoor sunlight and glare



Amber — ideal for low-light applications where enhanced contrast is needed



Gray — minimizes outdoor sunlight and glare



SCT-Reflect 50 — light mirror coating is ideal for varying light conditions



SCT-Gray — minimizes outdoor glare and offers true color recognition



SCT-Low IR — when peripheral IR protection is required



Shade 3.0 — welding shade for torch brazing operations



Shade 5.0 — welding shade for cutting operations



Uvex Livewire sealed eyewear comes complete with removable temples and headband.

ORDERING INFORMATION

EYEWEAR

ITEM #	FRAME COLOR	LENS TINT	LENS COATING	UPC CODE
S2600XP	Matte Black	Clear	Uvextreme Plus AF	603390129605
S2600D	Matte Black	Clear	Dura-streme HC/AF	603390129612
S2601XP	Matte Black	Espresso	Uvextreme Plus AF	603390129629
S2602XP	Matte Black	Amber	Uvextreme Plus AF	603390129636
S2604XP	Matte Black	SCT-Reflect 50	Uvextreme Plus AF	603390129643
S2605XP	Matte Black	SCT-Gray	Uvextreme Plus AF	603390129650
S2607XP	Matte Black	Shade 3.0	Uvextreme Plus AF	603390129667
S2608XP	Matte Black	Shade 5.0	Uvextreme Plus AF	603390129674
S2609XP	Matte Black	SCT-Low IR	Uvextreme Plus AF	603390129681
S2620XP	Silver	Clear	Uvextreme Plus AF	603390129698
S2621XP	Silver	Gray	Uvextreme Plus AF	603390129704
S2624XP	Silver	SCT-Reflect 50	Uvextreme Plus AF	603390129711

Packaging Information (Eyewear)
 Ind. box, 10/stocker, 200/case
 Case Weight: 35.6 lbs.
 Case Dimensions: 29" x 15" x 24"

Uvex® brand safety eyewear is offered for sale by Honeywell Safety Products exclusively in the Americas.



by Honeywell

FOR MORE INFORMATION, CONTACT:

Honeywell Safety Products

900 Douglas Pike

Smithfield, RI 02917-1874

800.430.5490 - US

800.446.1802 - Rx

888.212.7233 - Canada

www.uvex.us | www.uvexrx.com

uvex.us/livewire

Build a culture of safety. Honeywell can help.
 To learn more visit www.honeywellsafety.com/Culture

©2013 UVEX

UVEX.272

Honeywell