



Product Family
Uvex A400 Series








Sleek, wrap-around, one piece lens at an economical price.

[Learn more about all of our Uvex plano products at uvex.us >](http://uvex.us)

[Learn more about our Uvex Rx safety frames at uvexrx.com >](http://uvexrx.com)



Product Numbers & Ordering Information

	Product Numbers	Details
	A400	Clear Frame Clear Lens, Anti-scratch Coating
	A400AF	Clear Frame Clear Lens, Uvextra Anti-fog Coating
	A401	Gray Frame Gray Lens, Anti-scratch Coating
	A401AF	Gray Frame Gray Lens, Uvextra Anti-fog Coating
	A402	Amber Frame Amber Lens, Anti-scratch Coating
	A403	Gray Frame Silver Mirror Lens, Anti-scratch Coating
	A404	Clear Frame I/O Silver Mirror Lens, Anti-scratch Coating

Additional Information

800-430-5490 (US) or 888-212-7233 (CANADA)

Overview

Key Features

- Sporty, one piece wrap-around lens
- Available with scratch-resistant hardcoating or optional Uvextra anti-fog coating
- Meets ANSI and CSA standards

Hazards

- Abrasion
- Airborne Particulates
- Biohazard
- Impact

Regulations

- ANSI - Meets the ANSI Z87.1-2010 standard
- CSA Z94.3 - Tested by Honeywell to meet the requirements of the CSA Z94.3 standard

Warranty Information**LIMITED WARRANTY**

Uvex Eye and Face Protection, Inc. warrants that its products are free from defects in material and workmanship. A product that is the subject of a warranty claim must first be made available to an authorized Uvex distributor or to the seller from whom the product was purchased. All warranty returns must be shipped pre-paid. Uvex will then determine whether repair or replacement of the product is the appropriate remedy. This will be done at no charge to the end user. This limited warranty does not cover any Uvex Eye and Face product or component found to have been altered, misused, abused tampered with or improperly maintained or to have deteriorated due to aging of any components made of rubber

or any other elastomer. This limited warranty does not cover any damage, loss or expense due to damage caused by accident, abuse, improper maintenance, use or misuse of the product. Uvex Eye and Face products should only be used in strict accordance with and adherence to the detailed instructions and warnings provided with the product.

Specifications

Lens Overall Width

- 150mm

Lens Material

- Polycarbonate

Lens Coating

- Hardcoat, Uvextra Anti-fog coating

Lens Thickness

- 2.3mm

Available Lens Tints

- Clear, Gray, Amber, Silver Mirror, I/O Silver Mirror

Replacement Lenses Available (Yes/No)

- No

Rx Capable

- No

Temple Material

- Polycarbonate

Temple Length

- 125mm

Temple Set-back

- 60mm

Temple Style

- 1 piece

Spectacle Weight

- 26.5 grams

Frame Material

- Frameless Uni-lens

Available Frame Colors

- Clear, Gray, Amber

Dielectric Frame (Yes/No)

- Yes

Packaging

- 1/polybag, 200/case

Country of Origin

- China

MSDS Requirements

- None

WHMIS Requirements

- None

Harmonization Code

- 9004.90.0000

Training & Proper Use

Uvex A400 Series

All products come packaged with instructions and warnings for proper use.

© Honeywell International Inc.