


AERO

TGBX SERIES 4" & 10" Backsplash, Galv. Legs and Crossbracing

WORK TABLE



Item# _____ Project _____

Quantity	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #
24" WIDE				
_____	4TGBX-2424	3TGBX-2424	2TGBX-2424	1TGBX-2424
_____	4TGBX-2430	3TGBX-2430	2TGBX-2430	1TGBX-2430
_____	4TGBX-2436	3TGBX-2436	2TGBX-2436	1TGBX-2436
_____	4TGBX-2448	3TGBX-2448	2TGBX-2448	1TGBX-2448
_____	4TGBX-2460	3TGBX-2460	2TGBX-2460	1TGBX-2460
_____	4TGBX-2472	3TGBX-2472	2TGBX-2472	1TGBX-2472
_____	4TGBX-2484	3TGBX-2484	2TGBX-2484	1TGBX-2484
_____	4TGBX-2496	3TGBX-2496	2TGBX-2496	1TGBX-2496
_____	4TGBX-24108	3TGBX-24108	2TGBX-24108	1TGBX-24108
_____	4TGBX-24120	3TGBX-24120	2TGBX-24120	1TGBX-24120
_____	4TGBX-24132	3TGBX-24132	2TGBX-24132	1TGBX-24132
_____	4TGBX-24144	3TGBX-24144	2TGBX-24144	1TGBX-24144

30" WIDE				
_____	4TGBX-3024	3TGBX-3024	2TGBX-3024	1TGBX-3024
_____	4TGBX-3030	3TGBX-3030	2TGBX-3030	1TGBX-3030
_____	4TGBX-3036	3TGBX-3036	2TGBX-3036	1TGBX-3036
_____	4TGBX-3048	3TGBX-3048	2TGBX-3048	1TGBX-3048
_____	4TGBX-3060	3TGBX-3060	2TGBX-3060	1TGBX-3060
_____	4TGBX-3072	3TGBX-3072	2TGBX-3072	1TGBX-3072
_____	4TGBX-3084	3TGBX-3084	2TGBX-3084	1TGBX-3084
_____	4TGBX-3096	3TGBX-3096	2TGBX-3096	1TGBX-3096
_____	4TGBX-30108	3TGBX-30108	2TGBX-30108	1TGBX-30108
_____	4TGBX-30120	3TGBX-30120	2TGBX-30120	1TGBX-30120
_____	4TGBX-30132	3TGBX-30132	2TGBX-30132	1TGBX-30132
_____	4TGBX-30144	3TGBX-30144	2TGBX-30144	1TGBX-30144

36" WIDE				
_____	4TGBX-3636	3TGBX-3636	2TGBX-3636	1TGBX-3636
_____	4TGBX-3648	3TGBX-3648	2TGBX-3648	1TGBX-3648
_____	4TGBX-3660	3TGBX-3660	2TGBX-3660	1TGBX-3660
_____	4TGBX-3672	3TGBX-3672	2TGBX-3672	1TGBX-3672
_____	4TGBX-3684	3TGBX-3684	2TGBX-3684	1TGBX-3684
_____	4TGBX-3696	3TGBX-3696	2TGBX-3696	1TGBX-3696
_____	4TGBX-36108	3TGBX-36108	2TGBX-36108	1TGBX-36108
_____	4TGBX-36120	3TGBX-36120	2TGBX-36120	1TGBX-36120
_____	4TGBX-36132	3TGBX-36132	2TGBX-36132	1TGBX-36132
_____	4TGBX-36144	3TGBX-36144	2TGBX-36144	1TGBX-36144

MATERIAL

TOP

- 1 1/8" turn down on 3 sides.
- Rear has a 4" splash.
- Two heavy gauge steel box channels on 24" wide tables for rigidity.
- Three heavy gauge steel box channels on 30" tables for rigidity.
- Four heavy gauge steel box channels on 36" tables for rigidity.
- Sound deadened between table top and channels.

Crossbracing

- 1 1/4" O.D. 16 gauge galvanized steel crossbracing,
- 1 1/8" I.D. aluminum castings at all leg intersections.

LEGS

- 1 1/2" O.D. 16 gauge galvanized steel tubing, complete with 1" adjustable, impact resistant, plastic feet.

DESIGN FEATURES

- Crossbracing is fully adjustable and flexible in design.
- All tables fully cartoned.
- Easily assembled.

EXCLUSIVE AERO SAFETY EDGE

- Table hemmed to eliminate cuts from rough edges.


CONSTRUCTION

- Top is polished to a #4 mill finish.
- Helicarc welded construction creates uniform, rock-solid unit.
- Gussets fully welded for extra rigidity.
- All tables shipped K.D.


AEROSPEC

- 1TGBX TABLES ARE **AEROSPEC DESIGNED**.
- In addition to above specifications:
- Three sides have a "V" countertop edge to inhibit spillage.
- Backsplash is 10" high including a 2" return on a 45 deg. angle.

SEE PAGES TS-5A & TS-5B
TO CUSTOMIZE YOUR
AERO TABLE



Adjustable
Undershelf
with Exclusive
AEROLock
Extrusion



Strongest Construction
in the Industry

SEE PAGES SP-6A & SP-6B
TO DESIGN YOUR
FLEXIBLE WORKCENTER

BUILT TO LAST A LIFETIME


email - sales@aeromfg.com

AERO MANUFACTURING COMPANY • 310 ALLWOOD ROAD, CLIFTON, NEW JERSEY 07012 • VOICE 973.473.5300 FAX 973.473.3794









DIMENSIONAL SPECIFICATIONS

TGBX SERIES 4" & 10" Backsplash, Galv. Legs and Crossbracing



- Tables over 72" in length are shipped with six legs.
- All feet have a full 1" adjustability.
- Crossbracing is fully adjustable.



A Width	B Length	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #	Ship Weight	Cubic Feet
24" WIDE							
24	24	4TGBX-2424	3TGBX-2424	2TGBX-2424	1TGBX-2424	50	3
24	30	4TGBX-2430	3TGBX-2430	2TGBX-2430	1TGBX-2430	55	3
24	36	4TGBX-2436	3TGBX-2436	2TGBX-2436	1TGBX-2436	66	4
24	48	4TGBX-2448	3TGBX-2448	2TGBX-2448	1TGBX-2448	81	5
24	60	4TGBX-2460	3TGBX-2460	2TGBX-2460	1TGBX-2460	95	7
24	72	4TGBX-2472	3TGBX-2472	2TGBX-2472	1TGBX-2472	113	8
24	84	4TGBX-2484	3TGBX-2484	2TGBX-2484	1TGBX-2484	135	9
24	96	4TGBX-2496	3TGBX-2496	2TGBX-2496	1TGBX-2496	150	11
24	108	4TGBX-24108	3TGBX-24108	2TGBX-24108	1TGBX-24108	165	12
24	120	4TGBX-24120	3TGBX-24120	2TGBX-24120	1TGBX-24120	268	13
24	132	4TGBX-24132	3TGBX-24132	2TGBX-24132	1TGBX-24132	301	15
24	144	4TGBX-24144	3TGBX-24144	2TGBX-24144	1TGBX-24144	316	16

A Width	B Length	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #	Ship Weight	Cubic Feet
30" WIDE							
30	24	4TGBX-3024	3TGBX-3024	2TGBX-3024	1TGBX-3024	56	3
30	30	4TGBX-3030	3TGBX-3030	2TGBX-3030	1TGBX-3030	70	4
30	36	4TGBX-3036	3TGBX-3036	2TGBX-3036	1TGBX-3036	77	5
30	48	4TGBX-3048	3TGBX-3048	2TGBX-3048	1TGBX-3048	92	7
30	60	4TGBX-3060	3TGBX-3060	2TGBX-3060	1TGBX-3060	111	8
30	72	4TGBX-3072	3TGBX-3072	2TGBX-3072	1TGBX-3072	129	10
30	84	4TGBX-3084	3TGBX-3084	2TGBX-3084	1TGBX-3084	153	12
30	96	4TGBX-3096	3TGBX-3096	2TGBX-3096	1TGBX-3096	171	13
30	108	4TGBX-30108	3TGBX-30108	2TGBX-30108	1TGBX-30108	195	15
30	120	4TGBX-30120	3TGBX-30120	2TGBX-30120	1TGBX-30120	294	17
30	132	4TGBX-30132	3TGBX-30132	2TGBX-30132	1TGBX-30132	331	18
30	144	4TGBX-30144	3TGBX-30144	2TGBX-30144	1TGBX-30144	346	20

A Width	B Length	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #	Ship Weight	Cubic Feet
36" WIDE							
36	36	4TGBX-3636	3TGBX-3636	2TGBX-3636	1TGBX-3636	92	6
36	48	4TGBX-3648	3TGBX-3648	2TGBX-3648	1TGBX-3648	101	8
36	60	4TGBX-3660	3TGBX-3660	2TGBX-3660	1TGBX-3660	121	10
36	72	4TGBX-3672	3TGBX-3672	2TGBX-3672	1TGBX-3672	142	12
36	84	4TGBX-3684	3TGBX-3684	2TGBX-3684	1TGBX-3684	169	14
36	96	4TGBX-3696	3TGBX-3696	2TGBX-3696	1TGBX-3696	189	16
36	108	4TGBX-36108	3TGBX-36108	2TGBX-36108	1TGBX-36108	160	18
36	120	4TGBX-36120	3TGBX-36120	2TGBX-36120	1TGBX-36120	315	20
36	132	4TGBX-36132	3TGBX-36132	2TGBX-36132	1TGBX-36132	358	22
36	144	4TGBX-36144	3TGBX-36144	2TGBX-36144	1TGBX-36144	373	24

All dimensions are typical (tol. ±1/8"). • For Accessories and Options see pages TS-5A & TS-5B.

email - sales@aeromfg.com

AERO MANUFACTURING COMPANY • 310 ALLWOOD ROAD, CLIFTON, NEW JERSEY 07012 • VOICE 973473.5300 FAX 973.473.3794