


AERO

TSB SERIES 4" & 10" Backsplash, Stainless Steel Undershelf

WORK TABLE



Item# _____ Project _____

Quantity	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #
24" WIDE				
—	4TSB-2424	3TSB-2424	2TSB-2424	1TSB-2424
—	4TSB-2430	3TSB-2430	2TSB-2430	1TSB-2430
—	4TSB-2436	3TSB-2436	2TSB-2436	1TSB-2436
—	4TSB-2448	3TSB-2448	2TSB-2448	1TSB-2448
—	4TSB-2460	3TSB-2460	2TSB-2460	1TSB-2460
—	4TSB-2472	3TSB-2472	2TSB-2472	1TSB-2472
—	4TSB-2484	3TSB-2484	2TSB-2484	1TSB-2484
—	4TSB-2496	3TSB-2496	2TSB-2496	1TSB-2496
—	4TSB-24108	3TSB-24108	2TSB-24108	1TSB-24108
—	4TSB-24120	3TSB-24120	2TSB-24120	1TSB-24120
—	4TSB-24132	3TSB-24132	2TSB-24132	1TSB-24132
—	4TSB-24144	3TSB-24144	2TSB-24144	1TSB-24144

Quantity	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #
30" WIDE				
—	4TSB-3024	3TSB-3024	2TSB-3024	1TSB-3024
—	4TSB-3030	3TSB-3030	2TSB-3030	1TSB-3030
—	4TSB-3036	3TSB-3036	2TSB-3036	1TSB-3036
—	4TSB-3048	3TSB-3048	2TSB-3048	1TSB-3048
—	4TSB-3060	3TSB-3060	2TSB-3060	1TSB-3060
—	4TSB-3072	3TSB-3072	2TSB-3072	1TSB-3072
—	4TSB-3084	3TSB-3084	2TSB-3084	1TSB-3084
—	4TSB-3096	3TSB-3096	2TSB-3096	1TSB-3096
—	4TSB-30108	3TSB-30108	2TSB-30108	1TSB-30108
—	4TSB-30120	3TSB-30120	2TSB-30120	1TSB-30120
—	4TSB-30132	3TSB-30132	2TSB-30132	1TSB-30132
—	4TSB-30144	3TSB-30144	2TSB-30144	1TSB-30144

Quantity	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #
36" WIDE				
—	4TSB-3636	3TSB-3636	2TSB-3636	1TSB-3636
—	4TSB-3648	3TSB-3648	2TSB-3648	1TSB-3648
—	4TSB-3660	3TSB-3660	2TSB-3660	1TSB-3660
—	4TSB-3672	3TSB-3672	2TSB-3672	1TSB-3672
—	4TSB-3684	3TSB-3684	2TSB-3684	1TSB-3684
—	4TSB-3696	3TSB-3696	2TSB-3696	1TSB-3696
—	4TSB-36108	3TSB-36108	2TSB-36108	1TSB-36108
—	4TSB-36120	3TSB-36120	2TSB-36120	1TSB-36120
—	4TSB-36132	3TSB-36132	2TSB-36132	1TSB-36132
—	4TSB-36144	3TSB-36144	2TSB-36144	1TSB-36144

MATERIAL

- TOP**
- 1 1/2" turn down on 3 sides.
 - Rear has a 4" splash.
 - Two heavy gauge steel box channels on 24" wide tables for rigidity.
 - Three heavy gauge steel box channels on 30" tables for rigidity.
 - Four heavy gauge steel box channels on 36" tables for rigidity.
 - Sound deadened between table top and channels.
- SHELF**
- 18 gauge 430 series stainless steel.
- LEGS**
- 1 1/2" O.D. 16 gauge 304 series stainless steel tubing, complete with 1" adjustable, impact resistant, white metal feet.

DESIGN FEATURES

- Undershelf is the largest in the industry.
- Undershelf is fully adjustable and flexible in design.
- All tables fully cartoned.
- Easily assembled.

EXCLUSIVE AERO SAFETY EDGE

- Table and undershelf hemmed to eliminate cuts from rough edges.

CONSTRUCTION


- Top is polished to a #4 mill finish.
- Heliarc welded construction creates uniform, rock-solid unit.
- Gussets fully welded for extra rigidity.
- All tables shipped K.D.

AEROSPEC


- 1TSB TABLES ARE **AEROSPEC DESIGNED**.
- In addition to above specifications;
- Three sides have a "V" countertop edge to inhibit spillage.
- Backsplash is 10" high including a 2" return on a 45 deg. angle.
- Stainless steel gussets in lieu of galvanized.
- Stainless steel feet in lieu of white metal.

SEE PAGES TS-5A & TS-5B
TO CUSTOMIZE YOUR
AERO TABLE

SEE PAGES SP-6A & SP-6B
TO DESIGN YOUR
FLEXIBLE WORKCENTER



Adjustable Undershelf with Exclusive **AEROLOCK** Extrusion



Strongest Construction in the Industry

BUILT TO LAST A LIFETIME


email - sales@aeromfg.com

AERO MANUFACTURING COMPANY • 310 ALLWOOD ROAD, CLIFTON, NEW JERSEY 07012 • VOICE 973.473.5300 FAX 973.473.3794




DIMENSIONAL SPECIFICATIONS

TSB SERIES 4" & 10" Backsplash, Stainless Steel Undershaft



- Tables over 72" in length are shipped with six legs.
- Undershelf O.D. Table Length -2", Table Width -2".
- All feet have a full 1" adjustability.



A Width	B Length	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #	Ship Weight	Cubic Feet
24" WIDE							
24	24	4TSB-2424	3TSB-2424	2TSB-2424	1TSB-2424	50	5
24	30	4TSB-2430	3TSB-2430	2TSB-2430	1TSB-2430	55	6
24	36	4TSB-2436	3TSB-2436	2TSB-2436	1TSB-2436	66	7
24	48	4TSB-2448	3TSB-2448	2TSB-2448	1TSB-2448	81	9
24	60	4TSB-2460	3TSB-2460	2TSB-2460	1TSB-2460	95	12
24	72	4TSB-2472	3TSB-2472	2TSB-2472	1TSB-2472	113	14
24	84	4TSB-2484	3TSB-2484	2TSB-2484	1TSB-2484	135	16
24	96	4TSB-2496	3TSB-2496	2TSB-2496	1TSB-2496	150	18
24	108	4TSB-24108	3TSB-24108	2TSB-24108	1TSB-24108	165	21
24	120	4TSB-24120	3TSB-24120	2TSB-24120	1TSB-24120	268	28
24	132	4TSB-24132	3TSB-24132	2TSB-24132	1TSB-24132	301	36
24	144	4TSB-24144	3TSB-24144	2TSB-24144	1TSB-24144	316	39
30" WIDE							
30	24	4TSB-3024	3TSB-3024	2TSB-3024	1TSB-3024	56	6
30	30	4TSB-3030	3TSB-3030	2TSB-3030	1TSB-3030	70	7
30	36	4TSB-3036	3TSB-3036	2TSB-3036	1TSB-3036	77	9
30	48	4TSB-3048	3TSB-3048	2TSB-3048	1TSB-3048	92	11
30	60	4TSB-3060	3TSB-3060	2TSB-3060	1TSB-3060	111	14
30	72	4TSB-3072	3TSB-3072	2TSB-3072	1TSB-3072	129	17
30	84	4TSB-3084	3TSB-3084	2TSB-3084	1TSB-3084	153	20
30	96	4TSB-3096	3TSB-3096	2TSB-3096	1TSB-3096	171	22
30	108	4TSB-30108	3TSB-30108	2TSB-30108	1TSB-30108	195	25
30	120	4TSB-30120	3TSB-30120	2TSB-30120	1TSB-30120	294	40
30	132	4TSB-30132	3TSB-30132	2TSB-30132	1TSB-30132	331	43
30	144	4TSB-30144	3TSB-30144	2TSB-30144	1TSB-30144	346	47
36" WIDE							
36	36	4TSB-3636	3TSB-3636	2TSB-3636	1TSB-3636	92	10
36	48	4TSB-3648	3TSB-3648	2TSB-3648	1TSB-3648	101	14
36	60	4TSB-3660	3TSB-3660	2TSB-3660	1TSB-3660	121	17
36	72	4TSB-3672	3TSB-3672	2TSB-3672	1TSB-3672	142	20
36	84	4TSB-3684	3TSB-3684	2TSB-3684	1TSB-3684	160	23
36	96	4TSB-3696	3TSB-3696	2TSB-3696	1TSB-3696	169	27
36	108	4TSB-36108	3TSB-36108	2TSB-36108	1TSB-36108	189	30
36	120	4TSB-36120	3TSB-36120	2TSB-36120	1TSB-36120	315	46
36	132	4TSB-36132	3TSB-36132	2TSB-36132	1TSB-36132	358	51
36	144	4TSB-36144	3TSB-36144	2TSB-36144	1TSB-36144	373	55

All dimensions are typical (tol. ±1/8"). • For Accessories and Options see pages TS-5A, TS-5B.

email - sales@aeromfg.com

AERO MANUFACTURING COMPANY • 310 ALLWOOD ROAD, CLIFTON, NEW JERSEY 07012 • VOICE 973.473.5300 FAX 973.473.3794