


AERO

WORK TABLE

TGX SERIES Flat Top, Galvanized Legs and Crossbracing



Item# _____ Project _____

Quantity	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #
24" WIDE				
—	4TGX-2424	3TGX-2424	2TGX-2424	1TGX-2424
—	4TGX-2430	3TGX-2430	2TGX-2430	1TGX-2430
—	4TGX-2436	3TGX-2436	2TGX-2436	1TGX-2436
—	4TGX-2448	3TGX-2448	2TGX-2448	1TGX-2448
—	4TGX-2460	3TGX-2460	2TGX-2460	1TGX-2460
—	4TGX-2472	3TGX-2472	2TGX-2472	1TGX-2472
—	4TGX-2484	3TGX-2484	2TGX-2484	1TGX-2484
—	4TGX-2496	3TGX-2496	2TGX-2496	1TGX-2496
—	4TGX-24108	3TGX-24108	2TGX-24108	1TGX-24108
—	4TGX-24120	3TGX-24120	2TGX-24120	1TGX-24120
—	4TGX-24132	3TGX-24132	2TGX-24132	1TGX-24132
—	4TGX-24144	3TGX-24144	2TGX-24144	1TGX-24144

30" WIDE				
—	4TGX-3024	3TGX-3024	2TGX-3024	1TGX-3024
—	4TGX-3030	3TGX-3030	2TGX-3030	1TGX-3030
—	4TGX-3036	3TGX-3036	2TGX-3036	1TGX-3036
—	4TGX-3048	3TGX-3048	2TGX-3048	1TGX-3048
—	4TGX-3060	3TGX-3060	2TGX-3060	1TGX-3060
—	4TGX-3072	3TGX-3072	2TGX-3072	1TGX-3072
—	4TGX-3084	3TGX-3084	2TGX-3084	1TGX-3084
—	4TGX-3096	3TGX-3096	2TGX-3096	1TGX-3096
—	4TGX-30108	3TGX-30108	2TGX-30108	1TGX-30108
—	4TGX-30120	3TGX-30120	2TGX-30120	1TGX-30120
—	4TGX-30132	3TGX-30132	2TGX-30132	1TGX-30132
—	4TGX-30144	3TGX-30144	2TGX-30144	1TGX-30144

36" WIDE				
—	4TGX-3636	3TGX-3636	2TGX-3636	1TGX-3636
—	4TGX-3648	3TGX-3648	2TGX-3648	1TGX-3648
—	4TGX-3660	3TGX-3660	2TGX-3660	1TGX-3660
—	4TGX-3672	3TGX-3672	2TGX-3672	1TGX-3672
—	4TGX-3684	3TGX-3684	2TGX-3684	1TGX-3684
—	4TGX-3696	3TGX-3696	2TGX-3696	1TGX-3696
—	4TGX-36108	3TGX-36108	2TGX-36108	1TGX-36108
—	4TGX-36120	3TGX-36120	2TGX-36120	1TGX-36120
—	4TGX-36132	3TGX-36132	2TGX-36132	1TGX-36132
—	4TGX-36144	3TGX-36144	2TGX-36144	1TGX-36144

42" WIDE				
—	N.A.	N.A.	2TGX-4248	1TGX-4248
—	N.A.	N.A.	2TGX-4260	1TGX-4260
—	N.A.	N.A.	2TGX-4272	1TGX-4272
—	N.A.	N.A.	2TGX-4284	1TGX-4284
—	N.A.	N.A.	2TGX-4296	1TGX-4296
—	N.A.	N.A.	2TGX-42108	1TGX-42108
—	N.A.	N.A.	2TGX-42120	1TGX-42120
—	N.A.	N.A.	2TGX-42132	1TGX-42132
—	N.A.	N.A.	2TGX-42144	1TGX-42144

***FOR 48" WIDE TABLES SEE PRICE LIST**

MATERIAL

TOP

- 1 1/2" turn down on 4 sides.
- Two heavy gauge steel box channels on 24" wide tables for rigidity.
- Three heavy gauge steel box channels on 30" tables for rigidity.
- Four heavy gauge steel box channels on 36" and 42" tables for rigidity.
- Sound deadened between table top and channels.

Crossbracing

- 1 1/2" O.D. 16 gauge galvanized steel crossbracing, 1 1/2" I.D. aluminum castings at all leg intersections.

LEGS

- 1 1/2" O.D. 16 gauge galvanized steel tubing, complete with 1" adjustable, impact resistant, plastic feet.

DESIGN FEATURES

- Crossbracing is fully adjustable and flexible in design.
- All tables fully cartoned.
- Easily assembled.

EXCLUSIVE AERO SAFETY EDGE

- Table hemmed to eliminate cuts from rough edges.


CONSTRUCTION

- Top is polished to a #4 mill finish.
- Heliarc welded construction creates uniform, rock-solid unit.
- Gussets fully welded for extra rigidity.
- All tables shipped K.D.


AEROSPEC

- 1TGX TABLES ARE **AEROSPEC DESIGNED**.
In addition to above specifications:
- All four sides have a "V" countertop edge to inhibit spillage.

SEE PAGES SP-6A & SP-6B
TO DESIGN YOUR
FLEXIBLE WORKCENTER



Adjustable
Undershelf
with Exclusive
AEROLock
Extrusion



Strongest Construction
in the Industry

BUILT TO LAST A LIFETIME

email - sales@aeromfg.com

AERO MANUFACTURING COMPANY • 310 ALLWOOD ROAD, CLIFTON, NEW JERSEY 07012 • VOICE 973.473.5300 FAX 973.473.3794

© Copyright 2001 Aero Manufacturing Company, Inc.



Specifications subject to change without notice.

Page T-7A






DIMENSIONAL SPECIFICATIONS

TGX SERIES Flat Top, Galvanized Legs and Crossbracing



- Tables over 72" in length are shipped with six legs.
- All feet have a full 1" adjustability.
- Crossbracing is fully adjustable.



A Width	B Length	ECONOMY 16GA 430 Model #	DELUX 16GA 304 Model #	PREMIUM 14GA 304 Model #	AEROSPEC 14GA 304 Model #	Ship Weight	Cubic Feet
---------	----------	--------------------------	------------------------	--------------------------	---------------------------	-------------	------------

24" WIDE							
24	24	4TGX-2424	3TGX-2424	2TGX-2424	1TGX-2424	25	3
24	30	4TGX-2430	3TGX-2430	2TGX-2430	1TGX-2430	42	3
24	36	4TGX-2436	3TGX-2436	2TGX-2436	1TGX-2436	53	4
24	48	4TGX-2448	3TGX-2448	2TGX-2448	1TGX-2448	64	5
24	60	4TGX-2460	3TGX-2460	2TGX-2460	1TGX-2460	74	7
24	72	4TGX-2472	3TGX-2472	2TGX-2472	1TGX-2472	85	8
24	84	4TGX-2484	3TGX-2484	2TGX-2484	1TGX-2484	103	9
24	96	4TGX-2496	3TGX-2496	2TGX-2496	1TGX-2496	114	11
24	108	4TGX-24108	3TGX-24108	2TGX-24108	1TGX-24108	130	12
24	120	4TGX-24120	3TGX-24120	2TGX-24120	1TGX-24120	227	13
24	132	4TGX-24132	3TGX-24132	2TGX-24132	1TGX-24132	251	15
24	144	4TGX-24144	3TGX-24144	2TGX-24144	1TGX-24144	266	16

30" WIDE							
30	24	4TGX-3024	3TGX-3024	2TGX-3024	1TGX-3024	47	3
30	30	4TGX-3030	3TGX-3030	2TGX-3030	1TGX-3030	52	4
30	36	4TGX-3036	3TGX-3036	2TGX-3036	1TGX-3036	59	5
30	48	4TGX-3048	3TGX-3048	2TGX-3048	1TGX-3048	72	7
30	60	4TGX-3060	3TGX-3060	2TGX-3060	1TGX-3060	85	8
30	72	4TGX-3072	3TGX-3072	2TGX-3072	1TGX-3072	93	10
30	84	4TGX-3084	3TGX-3084	2TGX-3084	1TGX-3084	113	12
30	96	4TGX-3096	3TGX-3096	2TGX-3096	1TGX-3096	126	13
30	108	4TGX-30108	3TGX-30108	2TGX-30108	1TGX-30108	150	15
30	120	4TGX-30120	3TGX-30120	2TGX-30120	1TGX-30120	261	17
30	132	4TGX-30132	3TGX-30132	2TGX-30132	1TGX-30132	268	18
30	144	4TGX-30144	3TGX-30144	2TGX-30144	1TGX-30144	283	20

36" WIDE							
36	36	4TGX-3636	3TGX-3636	2TGX-3636	1TGX-3636	75	6
36	48	4TGX-3648	3TGX-3648	2TGX-3648	1TGX-3648	82	8
36	60	4TGX-3660	3TGX-3660	2TGX-3660	1TGX-3660	96	10
36	72	4TGX-3672	3TGX-3672	2TGX-3672	1TGX-3672	108	12
36	84	4TGX-3684	3TGX-3684	2TGX-3684	1TGX-3684	127	14
36	96	4TGX-3696	3TGX-3696	2TGX-3696	1TGX-3696	140	16
36	108	4TGX-36108	3TGX-36108	2TGX-36108	1TGX-36108	165	18
36	120	4TGX-36120	3TGX-36120	2TGX-36120	1TGX-36120	261	20
36	132	4TGX-36132	3TGX-36132	2TGX-36132	1TGX-36132	290	22
36	144	4TGX-36144	3TGX-36144	2TGX-36144	1TGX-36144	305	24

42" WIDE							
42	48	N.A.	N.A.	2TGX-4248	1TGX-4248	128	9
42	60	N.A.	N.A.	2TGX-4260	1TGX-4260	148	12
42	72	N.A.	N.A.	2TGX-4272	1TGX-4272	170	14
42	84	N.A.	N.A.	2TGX-4284	1TGX-4284	206	16
42	96	N.A.	N.A.	2TGX-4296	1TGX-4296	228	19
42	108	N.A.	N.A.	2TGX-42108	1TGX-42108	260	21
42	120	N.A.	N.A.	2TGX-42120	1TGX-42120	454	23
42	132	N.A.	N.A.	2TGX-42132	1TGX-42132	517	26
42	144	N.A.	N.A.	2TGX-42144	1TGX-42144	532	28

All dimensions are typical (tol. ±1/8"). • For Accessories and Options see pages TS-5A, TS-5B.
email - sales@aeromfg.com

AERO MANUFACTURING COMPANY • 310 ALLWOOD ROAD, CLIFTON, NEW JERSEY 07012 • VOICE 973.473.5300 FAX 973.473.3794