

# HONEYWELL MAXIMUM

Maximum Attenuation. Comfortable fit.



MAX-1 / NRR 33 (shown)

The world's most popular polyurethane foam earplug, Honeywell Maximum offers superior attenuation in a single-use earplug, delivering superior long-wearing comfort and solid performance that your workers can depend on.

## FEATURES:

- Bell flared shape provides superior attenuation.
- The worlds most used polyurethane earplug.
- Improves design which is easier to insert and reduces the tendency to back out of the ear.
- Smooth, solid resistant skin prevents dirt build up.
- Corded and uncorded versions available with various dispensing options.

## APPLICATIONS:

Any noise environment 105dB to less than 110dB.

## HYGIENE:

To maintain hygiene standards, Single-Use earplugs should be discarded at the end of every shift.

## TECHNICAL DETAILS:


Material:	Polyurethane foam
Diameter:	12.76mm
Length:	23.63mm
Cord length:	723.9mm
Cord material:	PVC
Temperature:	-26°C to +60°

## STANDARDS:

Approved to AS/NZS 1270:2002  
License number 1579  
SLC80 26dB Class 5

## CARE & MAINTENANCE:

Inspect prior to fitting, examine your earplugs for dirt, damage or extreme hardness—discard immediately if compromised.



## HONEYWELL MAXIMUM ORDERING INFORMATION

PART NUMBER	DESCRIPTION	PAIRS PER CASE
MAX-1	Uncorded, Individual poly bag, MAXIMUM, 200 pr/box	2000
MAX-30	Polycord, Individual poly bag, MAXIMUM, 100 pr/box	1000
MAX-1-D	Uncorded, LS-500 refill, MAXIMUM, 500 pr/box	2000
HL400-MAX-INTRO-AM	HL400 Dispenser, MAXIMUM, 400 pr	400
MAX-LS4-REFILL	Uncorded dispenser refill, MAXIMUM, 200 pr/bag	2000
HL400-MAX-REFILL	HL400 Canister Refill, MAXIMUM, 400 pr/canister	800
HL400-MAX-30-AM	HL400 Corded Dispenser, MAXIMUM, 400 pr	400
MAX-30-REFILL	Polycord, Individual poly bag, MAXIMUM, 400 pr/bag	2000
MAX-5-H5	Uncorded, 5 Pr poly bag, MAXIMUM, 50 bags/box	2500
MAX-5-30	Polycord, 5 Pr poly bag, MAXIMUM, 25 bags/box	1250

## For more information

Honeywell Personal Protective Equipment  
www.sps.honeywell.com  
Technical Service: 800.873.5242

Honeywell Maximum Sell Sheet | 01/2022  
© 2022 Honeywell International Inc.

**Honeywell**  
HOWARD  
LEIGHT