


EXTRA HEAVY DUTY

LOCKERS



Your team trusts you to provide a safe and secure environment while they focus on the job.

With durable, 14-gauge steel and best-in-class protection, these storage lockers offer a secure space for the things your team values.

- ✓ 25-YEAR WARRANTY
- ✓ EXTREME LOAD CAPACITIES
- ✓ SHIPS FULLY ASSEMBLED



HYBRID WELD DESIGN

MIG welded by hand and reinforced with rivets for extra durability

14-GAUGE STEEL

Extra Heavy Duty material provides added security and protection

WELDED LEAF HINGES

Innovative design keeps doors operating smoothly throughout the life of the product

RAISED LEG DESIGN

Makes for easy relocation with pallet jack or fork truck

CAST HANDLE

Sturdy, heavy design made for extensive use and securable with standard padlock

CABLE ACCESSIBLE

Conveniently placed pre-cut holes enables charging of personal items and power tools

VENTILATED OPTIONS

Punched hex ventilation available on select models for increased air flow

ELECTRONIC LOCK OPTIONS

Can be added to any locker for additional levels of security

SKU	Dimensions (W x D x OAH)	Number of Compartments	Load Capacity per Compartment*	Weight
-----	-----------------------------	---------------------------	-----------------------------------	--------



Single-Tier Storage Locker with Hooks				
1.66-1D-18-1T-L	18" x 18" x 75"	1	2000 lbs.	154 lbs.
26-1D-24-1T-L	24" x 24" x 75"	1	2000 lbs.	213 lbs.
36-2D-18-1T-L	36" x 18" x 75"	2	2000 lbs.	276 lbs.
46-2D-24-1T-L	48" x 24" x 75"	2	2000 lbs.	382 lbs.
4.66-3D-18-1T-L	54" x 18" x 75"	3	2000 lbs.	398 lbs.
66-3D-24-1T-L	72" x 24" x 75"	3	2000 lbs.	552 lbs.



Single-Tier Ventilated Locker with Hooks				
1.66-1H-18-1T-L	18" x 18" x 75"	1	2000 lbs.	138 lbs.
26-1H-24-1T-L	24" x 24" x 75"	1	2000 lbs.	185 lbs.
36-2H-18-1T-L	36" x 18" x 75"	2	2000 lbs.	250 lbs.
46-2H-24-1T-L	48" x 24" x 75"	2	2000 lbs.	336 lbs.
4.66-3H-18-1T-L	54" x 18" x 75"	3	2000 lbs.	361 lbs.
66-3H-24-1T-L	72" x 24" x 75"	3	2000 lbs.	488 lbs.



Double-Tier Storage Locker with Hooks				
1.66-2D-18-2T-L	18" x 18" x 75"	2	1000 lbs.	158 lbs.
26-2D-24-2T-L	24" x 24" x 75"	2	1000 lbs.	214 lbs.
36-4D-18-2T-L	36" x 18" x 75"	4	1000 lbs.	283 lbs.
46-4D-24-2T-L	48" x 24" x 75"	4	1000 lbs.	384 lbs.
4.66-6D-18-2T-L	54" x 18" x 75"	6	1000 lbs.	409 lbs.
66-6D-24-2T-L	72" x 24" x 75"	6	1000 lbs.	563 lbs.



Double-Tier Ventilated Locker with Hooks				
1.66-2H-18-2T-L	18" x 18" x 75"	2	1000 lbs.	143 lbs.
26-2H-24-2T-L	24" x 24" x 75"	2	1000 lbs.	187 lbs.
36-4H-18-2T-L	36" x 18" x 75"	4	1000 lbs.	258 lbs.
46-4H-24-2T-L	48" x 24" x 75"	4	1000 lbs.	341 lbs.
4.66-6H-18-2T-L	54" x 18" x 75"	6	1000 lbs.	374 lbs.
66-6H-24-2T-L	72" x 24" x 75"	6	1000 lbs.	493 lbs.



Three-Tier Storage Locker with Hooks				
1.66-3D-18-3T-L	18" x 18" x 75"	3	500 lbs.	170 lbs.
26-3D-24-3T-L	24" x 24" x 75"	3	500 lbs.	232 lbs.
36-6D-18-3T-L	36" x 18" x 75"	6	500 lbs.	307 lbs.
46-6D-24-3T-L	48" x 24" x 75"	6	500 lbs.	420 lbs.
4.66-9D-18-3T-L	54" x 18" x 75"	9	500 lbs.	444 lbs.
66-9D-24-3T-L	72" x 24" x 75"	9	500 lbs.	608 lbs.



Four-Tier Storage Locker				
1.66-4D-18-4T-L	18" x 18" x 75"	4	500 lbs.	182 lbs.
26-4D-24-4T-L	24" x 24" x 75"	4	500 lbs.	250 lbs.
36-8D-18-4T-L	36" x 18" x 75"	8	500 lbs.	332 lbs.
46-8D-24-4T-L	48" x 24" x 75"	8	500 lbs.	457 lbs.
4.66-12D-18-4T-L	54" x 18" x 75"	12	500 lbs.	481 lbs.
66-12D-24-4T-L	72" x 24" x 75"	12	500 lbs.	663 lbs.

* Single-Tier Lockers include one shelf per compartment with a load capacity of 1000 lbs. per shelf and 2000 lbs. per compartment