



Designed with proprietary Uvex® Floating Lens® technology, an expandable wrap-around brow, soft temple tip pads and nosepiece, the Uvex Protégé provides workers with exceptional comfort and flexible style. The Uvex Protégé delivers sport-styling, lightweight comfort and flexible design — all weighing less than an ounce. Comfort never felt so light.



SAFETY EYEWEAR

Uvex Protégé®

UVETM

by Honeywell

Uvex Protégé®

High Performance

- Available with Uvex high-performance Uvextreme® anti-fog and Ultra-dura® anti-scratch lens coatings as well as a wide range of lens tints to address the needs of a variety of work environments.
- Meets the ANSI Z87.1-2010 standard.
- Certified to the requirements of the CSA Z94.3 standard.
- Clear, Gray, Amber, Silver Mirror, and SCT-Reflect 50 tints meet Mil V₀ ballistic test for impact (protection against impact energies 7x higher than ANSI requirements).
- Lifetime frame guarantee.

Superior Comfort & Fit

- Proprietary Floating Lens® design offers increased flexibility in fit.
- Secure wrap-around brow expands to fit a wide range of users.
- Ultra lightweight design. At only 25 grams, it weighs less than one ounce.
- Soft temple tip pads provide a secure, comfortable fit.
- Comfortable nosepiece with soft, flexible "fingers" conforms to a variety of facial profiles and minimizes slippage.



Nosepiece with soft, flexible "fingers" conforms to a variety of facial profiles and minimizes slippage for all-day comfort.



Soft temple tip pads cushion the delicate area behind the ears, providing a secure, comfortable fit.



Floating Lens design offers increased flexibility for an accurate fit.



Secure wrap-around brow expands to fit a wide range of users.



Uvex Protégé®



Clear — Ideal for most indoor work applications



Amber — Ideal for low-light applications where enhanced contrast is needed



Gray — Minimizes outdoor sunlight and glare



SCT-Blue — Limits the effects of yellow or sodium vapor lighting which causes eye strain and fatigue



SCT-Reflect 50 — Light mirror coating is ideal for varying light conditions



Silver Mirror — Deflects sunlight and glare



SCT-Gray — Minimizes outdoor glare and offers true color recognition



All Uvex® lenses offer 99.9% ultra-violet protection.

ORDERING INFORMATION

EYEWEAR				
ITEM #	FRAME COLOR	LENS TINT	LENS COATING	UPC CODE
S4200	Metallic Black	Clear	Ultra-dura	603390120305
S4200X	Metallic Black	Clear	Uvextreme	603390120367
S4201	Metallic Black	Gray	Ultra-dura	603390120312
S4201X	Metallic Black	Gray	Uvextreme	603390120374
S4202	Metallic Black	SCT-Reflect 50	Ultra-dura	603390120329
S4203	Metallic Black	Silver Mirror	Ultra-dura	603390126017
S4205X	Metallic Black	SCT-Gray	Uvextreme	603390127502
S4221XC	Metallic Black	SCT-Blue	Ultra-dura	603390123665
S4221XXC	Metallic Black	SCT-Blue	Uvextreme	603390123672
S4222XC	Metallic Black	Amber	Ultra-dura	603390123689
S4222XXC	Metallic Black	Amber	Uvextreme	603390123696
S4210	Sandstone	Clear	Ultra-dura	603390120336
S4210X	Sandstone	Clear	Uvextreme	603390120381
S4211	Sandstone	Gray	Ultra-dura	603390120343
S4211X	Sandstone	Gray	Uvextreme	603390120398
S4212	Sandstone	SCT-Reflect 50	Ultra-dura	603390120350
S4213	Sandstone	Silver Mirror	Ultra-dura	603390126024

Packaging Information:
 Ind. polybag, 10/Stock, 200/Case
 Master Case Weight: 17 pounds
 Master Case Dimensions: 28" x 12" x 21"

Uvextreme® anti-fog coating performs under the most extreme conditions and will not wear off after repeated cleanings. It is permanently bonded to the lens and retains anti-scratch, anti-static and UV protection properties. Ultra-dura® hard coat is permanently bonded to the lens and is scratch-resistant and chemical-resistant.

UVEX[™]
 by Honeywell

FOR MORE INFORMATION, CONTACT:

Honeywell Safety Products
 900 Douglas Pike
 Smithfield, RI 02917-1874
 (800) 430-5490 - US
 (888) 212-7233 - Canada
www.uvex.us