

TORNADO MICROBURST

Ultra-
Compact
Scrubber

DELIVERING ULTRA-CLEAN FLOORS
IN AN ULTRA-COMPACT PACKAGE

Item# **TS040-W17-U**

Productivity

Cleans and dries floors with the efficiency of a scrubber in a lightweight, easy-to-use package. The intuitive, electronic controls are easy to master with minimal training time required.

Superior Performance

Featuring dual counter-rotating brushes driven by two powerful motors and an efficient vacuum and squeegee system, the Microburst achieves superior cleaning results and water removal to competitive models and is the ultimate upgrade from a mop and bucket.

Compact Design

The compact design and 360° maneuverability are perfectly suited for cleaning in tight spaces, while the small footprint and magnetic lock allows for easy storage and transport.

17.5"

Cleaning Path

90
min.

Battery Run
Time (ECO
Mode)

365/435
RPM

Brush Speed
(ECO/Reg.
Mode)

67
dB(A)

Sound Level



PRODUCT SPECIFICATIONS

Model TS040-W17-U

MACHINE DIMENSIONS

Dimensions (L x W x H) 17.9" x 13.9" x 46.8"

Weight 40 lbs

Solution Tank Capacity 1.3 gal

Recovery Tank Capacity 2.1 gal

DESIGN CHARACTERISTICS

Cleaning Path 17.5"

Brush Speed (ECO/
Power Mode) 365/435 RPM

Brush Type (2) 8.5" Standard Brushes

Down Pressure 45 lbs

Productivity
(Theoretical Max) 19,000 sq ft/hr

Sound Level 67 dB(A)

Battery Run Time 1.5 hrs

Battery Charge Time 3 hrs

Battery Power 36 V/8 Ah

Battery Type Lithium Iron Phosphate

Battery & Charger
Regulatory ETL Listed

Machine Regulatory ETL Listed

Dual Speed Yes

Electronic Control Panel Yes

REPLACEMENT ITEMS

Standard Brush Set TMS028

Squeegee Set TMS032

Battery MB027

Battery Charger TMS033

ACCESSORIES

Pad Driver Set TMS034

Mop Pad Set TMS035

Battery (MB027) sold separately.
Charger included with the machine.

Brushes come standard with unit;
optional pad drivers and mop pads for
buffing available to order.



Part # TMS034 & TMS035



Long-Lasting Battery

The rechargeable Lithium Iron Phosphate battery provides up to 1.5 hours of run time. Advantages of Lithium Iron Phosphate batteries include: extended longevity and cycle life, with the ability to withstand a large number of charge/discharge cycles, and enhanced thermal stability and safety, with a reduced risk of overheating.



Versatility

The dual-speed functionality (365 RPM ECO Mode, 435 RPM Reg. Mode) allows for effective cleaning of a variety of hard floor types and for extended battery life in ECO mode.



Easy Maintenance

The magnetically-mounted brushes and quick-release squeegee can be removed in seconds, allowing for swift and easy cleaning and maintenance.



Proven Safe

The Microburst is the only ultra-compact scrubber on the market with an ETL listed machine, battery and charger.



Larger Capacity

The detachable solution and recovery tanks are larger than competitive models (1.3 gal/2.1 gal) and are easy to remove, fill and empty with minimal downtime.



Intuitive Controls

The electronic control panel is simple to operate, with all the functions of the machine immediately accessible including power, brush, vacuum, solution flow, ECO mode, and battery charge indicator.



Brought to you by Tacony Corporation
www.TornadoVac.com
1-800-VACUUMS