



Riser Top Work Tables

Stainless Steel Work Tables



Use your smart phone to scan the above QR code to visit our website:
www.bk-resources.com

Certifications:



Features:

- Two (2) Sound Deadened Integrally Welded 5" "C" Channels to Reinforce and Maintain Level Working Surface
- Legs 1 5/8" Diameter
- 1 1/2" Splash Riser
- 84" & 96" Tables Have 6 Legs

Options:

- Single & Double Overshelves
- Drawer Assemblies
- Casters
- Upgraded Bullet Feet
- Extra Shelves
- Adjustable Table Mount Pot Rack



Material:




VTTR Series: S/S w/ Galvanized Legs & Undershelf

- T-430 18 ga. Stainless Steel Top
- Galvanized Legs & Adjustable Undershelf
- Adjustable High Impact Corrosion Resistant Feet

SVTR Series: S/S w/ Stainless Steel Legs & Undershelf

- T-430 18 ga. Stainless Steel Top
- Stainless Steel Legs & Adjustable Undershelf
- S/S Bullet Feet

Length	VTTR Series S/S w/ Galv. Legs & Undershelf			SVTR Series S/S w/ S/S Legs & Undershelf		
	T-430 S/S 18" Width	T-430 S/S 24" Width	T-430 S/S 30" Width	T-430 S/S 18" Width	T-430 S/S 24" Width	T-430 S/S 30" Width
24"	VTTR-1824	VTTR-2424	-	SVTR-1824	SVTR-2424	-
30"	VTTR-1830	VTTR-3024	VTTR-3030	SVTR-1830	SVTR-3024	SVTR-3030
36"	VTTR-1836	VTTR-3624	VTTR-3630	SVTR-1836	SVTR-3624	SVTR-3630
48"	VTTR-1848	VTTR-4824	VTTR-4830	SVTR-1848	SVTR-4824	SVTR-4830
60"	VTTR-1860	VTTR-6024	VTTR-6030	SVTR-1860	SVTR-6024	SVTR-6030
72"	VTTR-1872	VTTR-7224	VTTR-7230	SVTR-1872	SVTR-7224	SVTR-7230
84"	VTTR-1884	VTTR-8424	VTTR-8430	SVTR-1884	SVTR-8424	SVTR-8430
96"	VTTR-1896	VTTR-9624	VTTR-9630	SVTR-1896	SVTR-9624	SVTR-9630



TABLES 7 FT. AND LARGER ARE FURNISHED WITH SIX (6) LEGS

PRODUCT DATA SHEET

RESOURCES

