





Post-Mounted, Solar-Powered LED Safety Light

Tempest Solar-Powered Beacon

- Quickly deploy at a moments notice
- Attaches to top of Tempest Post with a simple twist
- Flashing beacon is perfect for safety warnings or as a guide path
- Use with belted Tempest posts for a highly visible safety barrier or with Tempest Sign Posts (No Belt) as a stand alone beacon
- Solar-powered battery yields up to 80 hours of light (with full-day charge)
- Powerful LED's emit 650 mcd with a visual distance of over 3,200 feet
- Outdoor Rated/Waterproof Level IP54
- Built-in sensor triggers light to flash at 100 LUX, saving battery life during daylight.
- Ni-MH Battery: 1.2V, 600 mA; Solar Panel: 3V, 120 mA



90-5004SB/YL



The Tempest Family of Products

The Tempest Post

The all-weather outdoor stanchion built for strength and endurance.



Part Number	Color	Type	Base Material	Belt Colors	Belt Length	Dims	Weight	Post Material
80-5000R/OR	Orange	Retractable Belt Post	Recycled Rubber	15 high-visibility colors PLUS choice of 2 safety messages	12 feet	38 1/4 inches tall, 16 wide at base	19 lbs.	HDPE Plastic
80-5000R/YL	Yellow							
80-5000R/BK	Black							
80-5002R/OR	Orange	Sign Stand		No Belts			18 lbs.	
80-5002R/YL	Yellow							
80-5002R/BK	Black							

Standard belt colors and messages:



Please Do Not Enter • Temporarily Closed

Please Do Not Enter • Temporarily Closed (Single-Sided Printing)

Caution • Please Do Not Enter

Caution • Please Do Not Enter (Single-Sided Printing)

The Tempest Beacon

Post mounted, solar-powered LED safety light



Battery Type	Solar Panel	Battery Life	Light Distance	Brightness	Outdoor/Waterproof
Ni-MH Battery: 1.2V, 600 mA	3V, 120mA	Up to 80 Hours	LED 650 mcd/visual distance of over 3,200 feet	100 LUX	Level IP54

Tempest Signage

Add important messaging to your queue or barrier



Front Message	Back Message	Single Sided	Double Sided	Part Number By Size		
				7x11	8.5x11	11x14
Enter	—	✓		80-1130TV/P1S	80-1141TV/P1S	80-1131TV/P1S
Exit	—	✓		80-1130TV/P2S	80-1141TV/P2S	80-1131TV/P2S
Do Not Enter	—	✓		80-1130TV/P3S	80-1141TV/P3S	80-1131TV/P3S
Line Forms Here	—	✓		80-1130TV/P4S	80-1141TV/P4S	80-1131TV/P4S
Caution	—	✓		80-1130TV/P5S	80-1141TV/P5S	80-1131TV/P5S
Caution	Caution		✓	80-1130TV/P5D	80-1141TV/P5D	—
Please Wait Here	Not an Entrance		✓	80-1130TV/P6D	80-1141TV/P6D	—
Taxi Line	—			—	80-1141TV/P7S	—
Custom Message	Custom Message		✓	80-1130TV/CPD	80-1141TV/CPD	80-1131TV/CPD
Custom Message	—	✓		80-1130TV/CPS	80-1141TV/CPS	80-1131TV/CPS

*Signage, Sign Stands and Posts sold separately. All Tempests come with a 1-Year warranty on post and belt mechanisms.