



**Klondike® KD3 Series  
Black Safety Glasses with Clear  
Lenses  
Soft and secure TPR nose piece**

**5-position ratchet action spatula  
temples**

**DURAMASS®**  
*Scratch Resistant  
Lens Coating*



**Series**

***Klondike (KD3)***

**Inner Packaging**

***Dozen White Box***

**Category**

***Safety Glasses***

**Primary Frame Material**

***Nylon***

**Made In**

***Taiwan***

| <b>Product #</b> | <b>Lens Color</b> | <b>Lens Coating</b>       | <b>Scratch Resistant</b> | <b>VLT%</b> | <b>Frame Color</b> | <b>Temple Color</b> |
|------------------|-------------------|---------------------------|--------------------------|-------------|--------------------|---------------------|
| <b>K3H15A</b>    | <b>Amber</b>      | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>80</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>K3H20A</b>    | <b>Amber</b>      | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>80</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>KD314</b>     | <b>Amber</b>      | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>80</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>KD310</b>     | <b>Clear</b>      | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>90</b>   | <b>Black</b>       | <b>Black</b>        |



| <b>Product #</b> | <b>Lens Color</b>       | <b>Lens Coating</b>       | <b>Scratch Resistant</b> | <b>VLT%</b> | <b>Frame Color</b> | <b>Temple Color</b> |
|------------------|-------------------------|---------------------------|--------------------------|-------------|--------------------|---------------------|
| <b>K3H20</b>     | <b>Clear</b>            | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>90</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>K3H25</b>     | <b>Clear</b>            | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>90</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>K3H10</b>     | <b>Clear</b>            | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>90</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>K3H15</b>     | <b>Clear</b>            | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>90</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>KD310AF</b>   | <b>Clear</b>            | <b>Duramass Anti-Fog</b>  | <b>Yes</b>               | <b>90</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>K3H15G</b>    | <b>Gray</b>             | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>13</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>K3H25G</b>    | <b>Gray</b>             | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>13</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>KD312</b>     | <b>Gray</b>             | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>13</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>K3H10G</b>    | <b>Gray</b>             | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>13</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>K3H20G</b>    | <b>Gray</b>             | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>13</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>KD312AF</b>   | <b>Gray</b>             | <b>Duramass Anti-Fog</b>  | <b>Yes</b>               | <b>13</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>KD313</b>     | <b>Light Blue</b>       | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>68</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>KD319AF</b>   | <b>I/O Clear Mirror</b> | <b>UV-AF Anti-Fog</b>     | <b>Yes</b>               | <b>36</b>   | <b>Black</b>       | <b>Black</b>        |
| <b>KD319</b>     | <b>I/O Clear Mirror</b> | <b>Duramass Hard Coat</b> | <b>Yes</b>               | <b>36</b>   | <b>Black</b>       | <b>Black</b>        |

