


See what's ahead of you and around you with the intrinsically safe Dualie 3AA Magnet. It produces a focused spot light and soft flood light to illuminate your work area and help to avoid slips, trips and falls.

Now featuring a magnetic clip with integrated hang hook for hands-free use.



Simultaneous spot and flood modes = 245 total lumens

Rugged, integrated, clip conforms to body of light
Grabs onto shirts, pockets and other gear for hands-free use
Integrated magnets grab onto steel surfaces for hands-free use




Durable, non-conductive, corrosion-proof polymer resin
Rocky stipple texture for a sure grip

Unbreakable polycarbonate lens with scratch-resistant coating

Uses 3 "AA" alkaline batteries - affordable and easy-to-find; also accepts 3 "AA" lithium batteries

140 LUMENS
245 TOTAL LUMEN OUTPUT



Dual, independently operating push-button switches for spot beam, flood beam, or both beams simultaneously
Easy to use with gloves



Flood light produces a soft, wide beam to illuminate your work area



<p>Three output modes: Spot, flood, both (spot and flood simultaneously):</p> <ul style="list-style-type: none"> - Spot: 140 lumens; 7,300 candela; 171m beam distance; runs 18 hours - Flood: 140 lumens; 80 candela; 18m beam distance; runs 18 hours - Simultaneous spot beam and flood beam: 245 lumens; runs 9 hours <p>Spot beam utilizes smooth parabolic reflector for tight beam with optimum peripheral illumination</p> <p>Flood beam produces a soft, wide beam to illuminate your work area</p>
Spot and flood beams intersect for an uninterrupted light pattern to eliminate blind spots
One-handed operation of all lighting modes
Ergonomically designed for maximum hand comfort
IPX7 waterproof to 1m for 30 minutes; 2 meter impact resistance tested

<p>Operating temperature: -20°F to 130°F. (To maintain hazardous locations rating: -20°C to 40°C)</p>
<p>Class I, II, Division 1, Groups A, B, C, D, E, F, G; Class III; CL I, ZN 0, IIC; Exia; T-Code: T4</p>
<p>7.50" (19.05 cm); 7.1 oz (201g) AA alkaline batteries; 6.2 oz. (176g) AA lithium batteries</p>
<p>Limited Lifetime Warranty Visit www.streamlight.com for full warranty information</p>
<p>#68780 Dualie 3AA with magnetic clip and lanyard - Box - Yellow #68781 Dualie 3AA with magnetic clip and lanyard - Box - Black #68782 Dualie 3AA with alkaline batteries, magnetic clip and lanyard - Box - Yellow #68783 Dualie 3AA with alkaline batteries, magnetic clip and lanyard - Box - Black</p>