



# JACKSON<sup>®</sup>

**SAFETY**

Be Smart. Be Safe. Be Sure. 

## SC-6 Premium Cap-Style Slotted Hard Hat

### Key Features and Benefits:

- Jackson's most popular hard hat!
- Classic smooth dome shape for improved impact deflection
- Longer bill for improved protection from sun and falling debris
- Lightweight design is molded from high density polyethylene (HDPE)
- Comfortably fits head sizes 6-1/2 to 8
- Features Jackson's 370 Speed Dial ratcheting headgear – an industry best!
- Includes a replaceable extra-absorbent sweatband
- Meets **ANSI Z89.1, Type 1, Class C, G, and E**
- **CSA certified to CSA Z94.1, Type 1, Class E**
- Non-vented

**370<sup>™</sup>**  
**SPEED DIAL**  
 Premium 370 Speed Dial<sup>™</sup>  
 ratcheting headgear

Slotted cap allows use with dozens of Jackson hard hat accessories including our exclusive Hard Hat Interchange System

**MADE IN USA**



14833

Longer bill for improved protection from sun and falling debris

**\*\*\* BEST**




Smooth dome shape for improved impact deflection

Comfortable 4-pt. suspension



SC-6 Hard Hat works with the Hard Hat Interchange System



| Product Number | Color         | Suspension           | Case Count |
|----------------|---------------|----------------------|------------|
| 14833          | Yellow        | 4 pt. 370 Speed Dial | 12         |
| 14834          | White         | 4 pt. 370 Speed Dial | 12         |
| 14836          | Brown         | 4 pt. 370 Speed Dial | 12         |
| 14838          | Blue          | 4 pt. 370 Speed Dial | 12         |
| 14839          | Orange        | 4 pt. 370 Speed Dial | 12         |
| 14841          | Red           | 4 pt. 370 Speed Dial | 12         |
| 14842          | Gray          | 4 pt. 370 Speed Dial | 12         |
| 14843          | Hi-Vis Orange | 4 pt. 370 Speed Dial | 12         |

SureWerx USA Inc.  
 Elgin, IL 60123  
 Phone: (800) 323-7402  
 Fax: (847) 358-8564  
[www.surewerx.com/usa](http://www.surewerx.com/usa)





# JACKSON<sup>®</sup>

**SAFETY**

Be Smart. Be Safe. Be Sure. 

## Replacement Parts and Accessories



14841



14833



20776



14203



14235

| Replacement Parts & Accessories | Description   | Case Count |
|---------------------------------|---|------------|
| 14936                           | 4 pt. Suspension  | 6          |
| 14937                           | 2 pt. Chin Strap  | 12/Bag     |
| 14958                           | Sweatband   | 25/Bag     |
| 20776                           | Premium Dielectric Ear Muffs, Cap Mount 22 NRR Rating                                   | 20/Packs   |
| 14203                           | Maxview with HHIS Universal Hard Hat Slot Adaptor                                       | 4          |
| 14235                           | Quad 500 <sup>®</sup> w/Flip-Up SH 5 IR Window and HHIS Universal Hard Hat Slot Adaptor | 4          |
| 38425                           | Hard Hat Interchange Face Shield Kit  | 6          |



### Customize Your Hard Hat With Your Company Logo!

- Scan the barcode with your device
- Fill out the easy to use online form
- A proof will be returned within 24 hours



14958



38425