

Konftel Cam20

Show everyone. In the minutest detail.



The Konftel Cam20 is the conference camera that brings 4K Ultra HD video to huddle rooms and medium-sized meeting rooms. Coverage for all the participants, who are presented naturally in the pin-sharp image. In short, the Konftel Cam20 is the ideal complement to your speakerphone – the perfect huddle room camera.

You can also be sure that the other participants in the video conference will get a clear and balanced image of you and your colleagues – whether you opt to transmit in 4K or regular HD resolution. With WDR technology, the Konftel Cam20 automatically adjusts to achieve a good picture in different light conditions, even challenging ones such as low light, direct sunlight and high contrast.


4K 123° EPTZ

- 4K Ultra HD
- 123° field of view
- Simple installation
- EPTZ
- 8x digital zoom
- USB 3.0
- HDMI
- Simultaneous output signal via HDMI and USB
- Two-year warranty



IMPRESSIVE VIDEO QUALITY

The Konftel Cam20 is optimized for situations where the conference cam needs to be positioned close to the table, as is normal in today's many huddle rooms. The 123° field of view means that all the participants can sit in a comfortable position and still fit into the video image. At the same time, the camera creates a realistic image with no distortion.



SMOOTH MEETINGS

Whatever your preferred app or cloud service, the Konftel Cam20 will sort out the video image as long as you can connect via USB. Once the meeting is up and running, you can control the camera's digital Pan-Tilt-Zoom via the remote control with simple presets. 4K resolution makes the zoom deep and sharp.

Specifications Konftel Cam20

GENERAL

Product name: Konftel Cam20

Item number: 931201001

Contents: Konftel Cam20, 5 m USB cable (type A/ type B), remote control with two AAA batteries, Quick guide, safety declaration.

Product documentation: Manual, Quick guide

Size: 194 x 34 x 42 mm without bracket

Weight: 340 g

Color: Charcoal black

Warranty: 2 years

CAMERA

Resolution: 4K Ultra HD/30 fps

Zoom: 8x digital

Focus: Auto

Field of view: 123°

No. of presets: 255

Video format: YUY2, MJPEG, H.264, NV12

Camera control: UVC 1.5/IR Remote

CONNECTIVITY

USB: USB 3.0 type B

POWER SUPPLY

AC adapter: Delta ADP-30KR BD, 5V

Power consumption: 3W

SYSTEM REQUIREMENTS

Operating system: Windows 7, 8, 10, Mac OS X, Linux

ADDITIONAL FEATURES

Software updates: Yes

ENVIRONMENT

Temperature: -10°C ~ 40°C

View full spec at konftel.com

Accessories

KONFTEL OCC HUB

Item no.: 900102149

The heart of Konftel's video collaboration solutions. Connect the speakerphone, conference cam and screen with a single cable.



Collaboration solutions with the Konftel Cam20

SMALL



KONFTEL C20Ego

Huddle room video. Convenience in a box.

The Konftel C20Ego video collaboration kit teams the Konftel Cam20 with the brilliant Konftel Ego speakerphone with OmniSound® audio quality. The Konftel OCC Hub brings the whole package together, so a single USB cable is all you need to connect the conference cam, the audio device and the room's screen to the collaboration app on your laptop.

Meeting size: Up to 6 people

MEDIUM



KONFTEL C2055

All included

Konftel C2055 is the perfect video collaboration solution for medium-sized meeting rooms, combining the Konftel Cam20 4K conference camera and the Konftel 55 speakerphone with OmniSound® audio quality. The Konftel OCC Hub brings everything together into one convenient package, so a single USB cable is all you need to connect the camera, the audio device and the room's screen to the collaboration app on your laptop.

Meeting size: Up to 12 people

RETAILER SPACE

© Konftel AB. In line with our policy for continuous product development, we reserve the right to change the product specifications. Visit www.konftel.com for the latest information.

Konftel is a leading company within collaboration endpoint solutions. Since 1988, our mission has been to help people in businesses around the world to have meetings regardless of distance. Based on our success, we know that remote collaboration is a smooth way to save time, money and at the same time contribute to a more sustainable world. Crystal clear audio and a sharp video image are essential for efficient meetings, this is why we only focus on cutting-edge technology in our Collaboration Solutions. Our audio technology OmniSound® is built into all Konftel Conference phones and devices. The products are sold globally under the Konftel brand and our headquarter is based in Sweden. Read more about the company and our products at konftel.com.