



Highlights

- Ergonomic back-tilt keyboard tray with left or right mouse tray ensures wrists remain in a neutral position during data entry
- Patented counterbalance system provides smooth adjustment while maintaining touch-screen stability
- 9" (23 cm) vertical adjustment enhances ergonomics for multiple users
- Steel construction for long-lasting durability
- Easy to clean exterior

Patient Room:

- Side-to-side pan of keyboard and display promote patient caregiver interaction while accessing data
- Slide-out Keyboard Tray can extend out an extra 5" (13 cm) for comfortable data entry

High Traffic Areas:

- With the keyboard folded up, total system depth is as little as 4" (10,2 cm)

ergotron®

StyleView® Vertical Lift



Compact ergonomics, extremely low profile

PATIENT ROOM: Perfect for space constrained patient exam rooms, the low profile vertical lift provides 9" (23 cm) of smooth vertical adjustment and folds into a slim, compact unit when not in use. The slide-out, back-tilt keyboard enhances user comfort, while the monitor and keyboard pan capability promote patient caregiver interaction.

HIGH TRAFFIC AREAS: Perfect for space constrained high traffic areas, the low profile vertical lift provides 9" (23 cm) of smooth vertical adjustment and folds into a slim, compact unit when not in use—less than 4" (10,2 cm) from the wall. A unique cable management system hides unsightly cords and makes cleaning the unit a snap!

- 9" (23 cm) of smooth vertical adjustment easily accommodates average female to male users
- Fold-down keyboard tray
- Back-tilt keyboard tray adjustable 0 to -10°
- Mouse and scanner holder
- Integrated cable management system can be configured on either side
- Mounting Standards: VESA FDMI, MIS-D, 100/75, C (hole pattern: 100 x 100 mm & 75 x 75 mm)
- Warranty: five (5) years
- Vertical Lift Auto-Retracting Keyboard Kit (97-487-800)

Patient Room:

- Extends out 5" (13 cm) inches when in use
- Keyboard left/right panning up to 120°
- Monitor panning up to 50° (dependant on monitor size)

High Traffic Areas:

- Low profile (down to 4") for use in space-constrained areas or high-traffic areas



Product Name	StyleView Vertical Lift, Patient Room
Part Numbers	60-609-216 (white) 60-609-195 (black)
Product Includes	Slide out panning keyboard tray, mouse pad (built into the keyboard tray) wrist rest, mouse pouch, mouse and scanner holder
Shipping Dimensions	39.5" x 16" x 10.75" (1000 x 406 x 273 mm) LWH
Shipping Weight	35.5 lbs (16,1 kg)
Warranty	5 years
Weight Capacity	8-33 lbs (3,6-14,9 kg) Listed weight capacity represents total load on Vertical Lift, including both the monitor and contents of keyboard tray
Compatible Display(s)	VESA FDMI, MIS-D, 100/75, C (hole pattern: 100 x 100 mm & 75 x 75 mm) Larger display sizes may inhibit the keyboard tray folding flat in storage position

Product Name	StyleView Vertical Lift, High Traffic Areas
Part Numbers	60-593-216 (white) 60-593-195 (black)
Product Includes	Mouse pad, wrist rest, mouse pouch
Shipping Dimensions	39.5" x 16" x 10.75" (1000 x 406 x 273 mm) LWH
Shipping Weight	36.4 lbs (16,5 kg)
Warranty	5 years
Weight Capacity	5-30 lbs (2,3-13,6 kg) Listed weight capacity represents total load on Vertical Lift, including both the monitor and contents of keyboard tray
Compatible Display(s)	VESA FDMI, MIS-D, 100/75, C (hole pattern: 100 x 100 mm & 75 x 75 mm) Larger display sizes may inhibit the keyboard tray folding flat in storage position

© 2019 Ergotron, Inc. 01/01/2019-EA Literature made in the U.S.A.

Content is subject to change without notification

StyleView is a registered trademark of Ergotron, Inc. in the U.S.A. and China

Americas Sales and Corporate Headquarters

St. Paul, MN USA
(800) 888-8458
+1-651-681-7600
www.ergotron.com
sales@ergotron.com

EMEA Sales

Amersfoort, The Netherlands
+31 33 45 45 600
www.ergotron.com
info.eu@ergotron.com

APAC Sales

Tokyo, Japan
www.ergotron.com
apaccustomerservice@ergotron.com

Worldwide OEM Sales

www.ergotron.com
info.oem@ergotron.com

