

# COMBO L-SEALER AND SHRINK TUNNEL

Model: SS-1519EC-Series

Economical machine for low to medium production



- New design featuring “Micro-Knife” technology
  - Capable of 8-10 packages per minute
    - Seal size: 15”W x 19”L
  - Tunnel dimensions: 20”L x 16”W x 6”H
  - Tunnel features re-circulating air chamber
- Optional: magnet hold (Model: SS-1519ECM), power discharge conveyor (Model: SS-1519CMC)
- Recommended film: POF (PVC not recommended)

## More Details:

The SS-1519EC Series Semi-Automatic L-Bar Sealer w/ attached tunnel is a heavy duty production based unit designed to run 2 shifts per day if needed. With its heavy duty frame construction, cast aluminum seal head and Micro Knife Seal Technology you will get years of use with minimal repairs. This machine is capable of operating at speeds of 8-10 PPM.

We recommend this combo unit for POF film only and film gauge between 60-80G.

Tunnel features: Live roller rod conveyor with fully re-circulating air chamber, AC variable speed conveyor, 0-60 FPM, digital temperature control and automatic cool down with shut off.

Available in 110 volts or 220 volts. We highly recommend 220V as this will be a more efficient tunnel.

## Specifications:

POWER	110V / 1PHASE / 20AMPS <b>OR</b> 220V / 1PHASE / 45AMPS
WEIGHT	460-LBS
DIMENSIONS	76”L X 26”W X 50”H
SEAL SIZE	15”W X 19”L
TUNNEL OPENING	20”L X 16”W X 6”H
MAX. FILM WIDTH	22”
CAPABILITY	8-10 PACKAGES/MIN

# COMBO L-SEALER AND SHRINK TUNNEL

Model: SS-1519EC-Series



Tunnel Control Panel



Shown with:  
Optional SS-180-24  
Gravity Curved  
Conveyor



Sealer Control Panel



## Tunnel Features:

- Fully Re-Circulating Air Chambers
- AC Variable Speed Drive, 0-60FPM
- Live Roller Rod Conveyor
- Automatic Cool-Down w/ Shut-Off
- Digital Temperature Controller 0°F -400°F
- Anti-Jam Safety Feature on Conveyor



## Micro-Knife Technology

- Single Piece of PTFE Band Ribbon with Round Corner Seal – Reduces Dog Ears
- Will Seal PVC or Polyolefin Shrink Film
- 1 Year Warranty on Band Ribbon
- Option: Dual Magnet Hold Down (Model: SS-1519ECM)
- Option: Power Discharge Conveyor (Model: SS-1519ECMC)



## Pin Wheel Hole Punch

- Easy Load Film Rack
- Multiple Pin Wheels Provide Air Evacuation
- Adjustable Product Loading Tray