

# V-FORM™ Harness

Technical Data Sheet



<b>CAPACITY</b>	ANSI Z359.11: 130–310 lbs. (59–140 kg) OSHA / CSA Z259.10: 400 lbs. (180 kg)
<b>BRAND</b>	MSA
<b>SUB BRAND / MODEL NAME</b>	V-FORM
<b>SIZES</b>	Extra Small, Standard, Extra Large, Super Extra Large
<b>D-RING LOCATIONS</b>	Dorsal ( <i>back</i> ), hips, shoulders, chest
<b>LEG STRAP BUCKLE OPTIONS</b>	Tongue buckle, Qwik-Fit
<b>PADDING LOCATIONS</b>	Shoulders ( <i>optional</i> ), waist ( <i>construction version</i> )
<b>THREAD/STITCHING</b>	Polyester
<b>WEB</b>	Polyester
<b>WEB KEEPER</b>	Polyester, hook and loop closure
<b>LEG BUCKLES</b>	Steel and stainless steel
<b>CHEST BUCKLE</b>	Steel and stainless steel
<b>D-RING</b>	Steel and stainless steel (bent for easy connection)
<b>PRODUCT WEIGHT</b>	3.53 lbs.
<b>SHIPPING DIMENSIONS</b>	4.3" x 8.5" x 7.25"
<b>PRODUCT STYLES</b>	Racing style, vest style ( <i>front D-ring version</i> )
<b>STANDARDS</b>	ANSI Z359.11, CSA Z259.10, OSHA



ft. (m)	110 (50)	130 (59)	150 (68)	170 (77)	190 (86)	210 (95)	230 (105)	250 (114)	270 (123)	290 (132)	310 (141)	330 (150)	400 (181)
6'-6" (2.0)													
6'-4" (1.9)													
6'-2" (1.9)													SX-LARGE
6'-0" (1.8)													X-LARGE
5'-10" (1.8)													STANDARD
5'-8" (1.7)													SMALL/ X SMALL
5'-6" (1.7)													
5'-4" (1.6)													
5'-2" (1.6)													
5'-0" (1.5)													

Note: This Bulletin contains only a general description of the products shown. While uses and performance capabilities are described, under no circumstances shall the products be used by untrained or unqualified individuals and not until the product instructions including any warnings or cautions provided have been thoroughly read and understood. Only they contain the complete and detailed information concerning proper use and care of these products.



**MSA – The Safety Company**  
1000 Cranberry Woods Drive  
Cranberry Township, PA 16066 USA  
Phone 724-776-8600  
[www.MSAsafety.com](http://www.MSAsafety.com)

**U.S. Customer Service Center**  
Phone 1-800-MSA-2222  
Fax 1-800-967-0398

**MSA Canada**  
Phone 1-800-672-2222  
Fax 1-800-967-0398

**MSA Mexico**  
Phone 01 800 672 7222